

# VS-ASI-FC-TPE-UL-YE 1000M - Flat cable



1434662

<https://www.phoenixcontact.com/us/products/1434662>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



AS-Interface TPE flat conductor with UL in yellow, 2 x 1.5 mm<sup>2</sup>, 1000 m on disposable drum

## Commercial data

Item number	1434662
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356349307
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85444995
Country of origin	DE

# VS-ASI-FC-TPE-UL-YE 1000M - Flat cable



1434662

<https://www.phoenixcontact.com/us/products/1434662>

## Technical data

### Product properties

Product type	Data cable by the meter
Number of positions	2
Shielded	no

### Electrical properties

Rated voltage (III/3)	32 V
Rated surge voltage	2 kV

### Interfaces

Signal type/category	AS-Interface
----------------------	--------------

### Dimensions

Width	10 mm
Height	4 mm

### Cable/line

Cable length	1000 m
Cable weight	64 kg/km
Number of positions	2
Shielded	no
Conductor structure	2 x 1.5 mm <sup>2</sup>
Conductor type	Flat cable
Conductor structure signal line	84x 0.15 mm
AWG signal line	16
Conductor cross-section	1.5 mm <sup>2</sup>
Wire diameter incl. insulation	2.5 mm
Outer sheath, material	TPE
External sheath, color	lemon yellow RAL 1012
Conductor material	Bare Cu litz wires
Material wire insulation	TPE
Single wire, color	brown, blue
Thickness, insulation	approx. 0.50 mm
Max. conductor resistance	≤ 13.7 Ω/km
Insulation resistance	≥ 1 MΩ*km
Nominal voltage, cable	32 V
Test voltage	2000 V
Smallest bending radius, fixed installation	≥ 6 mm (one-time)
Dynamic load capacity (bending)	Max. bending cycles: 8000000, Bending radius: 75 mm, Traversing direction: horizontal, above the broadside, Traversing rate: 4 m/s, Acceleration: 4 m/s <sup>2</sup> Max. bending cycles: 10000000, Bending radius: 50 mm,

# VS-ASI-FC-TPE-UL-YE 1000M - Flat cable



1434662

<https://www.phoenixcontact.com/us/products/1434662>

	Traversing direction: vertical, above the broadside
Halogen-free	no
Flame resistance	UL 1581, Sec. 1061 (Cable Flame) IEC 60332-1-2
Resistance to oil	UL 1581, Sec. 480 (60 °C)
Other resistance	UV resistant
Special properties	UL-Style 2103 CSA-File LL55255-42
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -30 °C ... 105 °C (Cable, flexible installation)

## FO cable

Transmission medium	Copper
---------------------	--------

## Mechanical properties

Duty cycle testing	suitable for drag chain
--------------------	-------------------------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (fixed routing) -30 °C ... 105 °C (Flexibly installed)
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-30 °C ... 105 °C

## Standards and regulations

### Testing

Duty cycle testing	suitable for drag chain
--------------------	-------------------------

# VS-ASI-FC-TPE-UL-YE 1000M - Flat cable



1434662

<https://www.phoenixcontact.com/us/products/1434662>

## Classifications

### UNSPSC

UNSPSC 21.0	26121707
-------------	----------

# VS-ASI-FC-TPE-UL-YE 1000M - Flat cable



1434662

<https://www.phoenixcontact.com/us/products/1434662>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)