

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Pin, angled, M12-SPEEDCON, A-coding, THR and wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1437012 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB26 |
| Product key | ABQEGA |
| GTIN | 4046356438582 |
| Weight per piece (including packing) | 12.8 g |
| Weight per piece (excluding packing) | 9.41 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Lock nut is included in the scope of delivery |
|--------------------|---|

Mounting

| | |
|---------------|-------------------------|
| Mounting type | Rear mounting (M12 x 1) |
|---------------|-------------------------|

Product properties

| | |
|---------------------|-----------------------------------|
| Product type | Circular connectors (device side) |
| Number of positions | 8 |
| Shielded | yes |
| Coding | A |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Material specifications

| | |
|--|--------|
| Material Housing | GD-Zn |
| Material Housing surface | Ni |
| Material Insulating body | PA 6.6 |
| Material Contact | CuZn |
| Material Contact surface | Au |
| Material Seal | NBR |
| Flammability rating according to UL 94 | V0 |

Electrical properties

| | |
|-----------------------|----------------------------|
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 30 V |
| Nominal current I_N | 2 A |

Connection data

Conductor connection

| | |
|-------------------------|------------------------|
| Connection method | THR and wave soldering |
| Contact connection type | Pin |

Connector

Connection 1

| | |
|-------------|-----|
| Head design | Pin |
|-------------|-----|

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

| | |
|-------------------|----------|
| Head cable outlet | angled |
| Head thread type | M12 |
| Head locking type | SPEEDCON |
| Coding | A |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug / socket) |

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting

1437012

<https://www.phoenixcontact.com/us/products/1437012>

Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., A-coded, view plug side

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1437012>

|  UL Recognized Approval ID: E118976-20100522 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 30 V | 2 A | 24 | - |

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440110 |
| ECLASS-15.0 | 27440110 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003568 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-DSIV-MS-8CON-L90 SH SCO - Device connector rear mounting



1437012

<https://www.phoenixcontact.com/us/products/1437012>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 328cb693-aa04-4aef-aaf1-bdee1c058b3c |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com