SAC-5P-M12MS/ 3,5-927/M12FR VA - Sensor/actuator cable

1444898

https://www.phoenixcontact.com/us/products/1444898

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

5-pos. cable, shielded M12 plug, straight, A-coded, angled on shielded M12 socket , A-coded with VA knurl, length: 3.5 m

Commercial data

Item number	1444898
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CDD
GTIN	4046356575119
Weight per piece (including packing)	341.8 g
Weight per piece (excluding packing)	341.8 g
Country of origin	PL

Technical data

Product properties

Product type	Data cable preassembled

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com