

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable



1446650

<https://www.phoenixcontact.com/us/products/1446650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black, free cable end, on Valve connector C (8 mm), with 1 LED, Wiring: Z diode, cable length: 10 m

## Commercial data

Item number	1446650
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1DEA
GTIN	4046356640053
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

1446650

<https://www.phoenixcontact.com/us/products/1446650>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3
No. of cable outlets	1
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	V0
Seal material	TPU
Material housing valve plug	TPU
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	24 V AC
	24 V DC
Nominal current $I_N$	4 A

### Signaling

Status display	1 LED
Status display present	yes

### Connector

#### Connection 1

Type	free cable end
------	----------------

#### Connection 2

Type	Valve connector C (8 mm)
Number of positions	3
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)
Protective circuit	Z diode


### Cable/line

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable



1446650

<https://www.phoenixcontact.com/us/products/1446650>

Cable length	10 m
PVC, 0.75 mm <sup>2</sup> , black [534]	
Dimensional drawing	
Cable weight	49.1 kg/km
Number of positions	3
Shielded	no
Cable type	PVC, 0.75 mm <sup>2</sup> , black [534]
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Conductor cross-section	3x 0.75 mm <sup>2</sup>
Wire diameter incl. insulation	1.7 mm ±0.1 mm
External cable diameter	5.30 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	26 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km (at 20 °C)
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	27 mm
Flame resistance	DIN VDE 0482 DIN EN 50265-2-1 in acc. to UL VW1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
	-20 °C ... 85 °C (Valve connector)

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable



1446650

<https://www.phoenixcontact.com/us/products/1446650>

Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-15 °C ... 80 °C (Cable, flexible installation)

## Standards and regulations

Standard designation	Valve connector
Standards/specifications	EN 175301-803

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable

1446650

<https://www.phoenixcontact.com/us/products/1446650>


## Drawings

Dimensional drawing



Valve connector, type C

Dimensional drawing



Valve connector, type C, side view

1446650

<https://www.phoenixcontact.com/us/products/1446650>

Schematic diagram



Valve connector connector pin assignment, type C

Circuit diagram



Contact assignment of the valve plug

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable



1446650

<https://www.phoenixcontact.com/us/products/1446650>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

# SAC-3P-10,0-534/C-1L-Z - Sensor/actuator cable



1446650

<https://www.phoenixcontact.com/us/products/1446650>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)