

# SAC-2PY-M/0,53-910-F/0,2SHSCO - Bus system cable



1447060

<https://www.phoenixcontact.com/us/products/1447060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, PROFIBUS, 2-pos., PUR, halogen free, violet RAL 4001, shielded, straight M12 SPEEDCON plug, B-coded, to straight M12 SPEEDCON socket, B-coded and free cable end, cable length S1: 0.53 m, cable length S2: 0.2 m

## Commercial data

Item number	1447060
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1GAD
GTIN	4046356694674
Weight per piece (including packing)	108.6 g
Weight per piece (excluding packing)	108.6 g
Country of origin	PL

# SAC-2PY-M/0,53-910-F/0,2SHSCO - Bus system cable

1447060

<https://www.phoenixcontact.com/us/products/1447060>

## Technical data

### Product properties


Product type	Data cable preassembled
--------------	-------------------------

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Cable/line

#### PROFIBUS [910]

Dimensional drawing	
UL AWM Style	21198 (80°C/300 V)
Number of positions	2
Shielded	yes
Cable type	PROFIBUS [910]
Conductor structure	1x2xAWG24/19
AWG signal line	24
Conductor cross-section	2x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	2.55 mm ±0.05 mm
External cable diameter	7.70 mm ±0.02 mm
Outer sheath, material	PUR
External sheath, color	red lilac RAL 4001
Conductor material	Tin-plated Cu litz wires
Single wire, color	red, green
Overall twist	2 cores with 2 fillers to the core
Optical shield covering	80 %
Insulation resistance	≥ 5 GΩ*km
Wave impedance	150 Ω ±10 % (3 MHz ... 20 MHz)
Nominal voltage, cable	≤ 125 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Dynamic load capacity (bending)	Max. bending cycles: 4000000, Bending radius: 65 mm, Bending radius: 15 x D, Traversing path: 4.5 m, Traversing rate: 3 m/s,

# SAC-2PY-M/0,53-910-F/0,2SHSCO - Bus system cable



1447060

<https://www.phoenixcontact.com/us/products/1447060>

	Acceleration: 3 m/s <sup>2</sup>
Shield attenuation	≤ 4.9 dB (at 16 MHz)
	≤ 4.9 dB (at 4 MHz)
	≤ 0.5 dB (at 38.4 kHz)
	≤ 0.3 dB (at 9.6 kHz)
Halogen-free	in accordance with DIN VDE 0472 part 815
	according to IEC 60754-1
Flame resistance	UL 1581, Section 1060 and UL 2556, Section 9.3 (FT1)
	UL 1581, Section 1100 and UL 2556, Section 9.1 (HFT/FT2)
	IEC 60332-1-2
Resistance to oil	in accordance with DIN EN 60811-404
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-30 °C ... 70 °C (Cable, flexible installation)
	-20 °C ... 60 °C (for installation)
	-20 °C ... 60 °C (cable, drag chain applications)

# SAC-2PY-M/0,53-910-F/0,2SHSCO - Bus system cable



1447060

<https://www.phoenixcontact.com/us/products/1447060>

## Classifications

### ECLASS

ECLASS-13.0	27060313
ECLASS-15.0	27060313

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-2PY-M/0,53-910-F/0,2SHSCO - Bus system cable



1447060

<https://www.phoenixcontact.com/us/products/1447060>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	1,6,7,8,9,14,15,16,17,17,18,18-Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]octadeca-7,15-diene ("Dechlorane Plus" <sup>TM</sup> )(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	12e83296-c633-4a29-9a37-f5c1e09e5213

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)