


SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR/PVC, black-gray RAL 7021, free cable end, on Socket straight 1/2"-20UNF, coding: C, cable length: 10 m

Commercial data

Item number	1527029
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF09
Product key	AF1EBA
GTIN	4046356071857
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	C

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	≥ 10 MΩ
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight 1/2"-20UNF
Number of positions	3
Coding type	C

Cable/line

Cable length	10 m
--------------	------


PUR/PVC black [350]

SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

Dimensional drawing	
Cable weight	37 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR/PVC black [350]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	0.34 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm
External cable diameter	5.20 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	green, red-black, red-white
Thickness, insulation	approx. 0.30 mm (Core insulation) ≥ 0.38 mm (Outer cable sheath)
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≤ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	52 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 52 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Flame resistance	in accordance with DIN UL-Style 20549
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)

SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

-5 °C ... 80 °C (Cable, flexible installation)


SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable

1527029

<https://www.phoenixcontact.com/us/products/1527029>


Drawings

Dimensional drawing



1/2"-20UNF socket, straight

Schematic diagram



Pin assignment 1/2"-20UNF socket, 2-pos., view female side


SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

Circuit diagram



Contact assignment of 1/2" UNF plugs / sockets

SAC-3P-MICFS/10,0-PUR - Sensor/actuator cable



1527029

<https://www.phoenixcontact.com/us/products/1527029>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com