

SACC-CI M12FS-5CON 18,5 VPE1000 - Contact carrier



1545399

<https://www.phoenixcontact.com/us/products/1545399>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 5-position

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1545399 |
| Packing unit | 1,000 pc |
| Minimum order quantity | 1,000 pc |
| Sales key | AB28 |
| Product key | ABQZFA |
| GTIN | 4046356178389 |
| Weight per piece (including packing) | 1.78 g |
| Weight per piece (excluding packing) | 1.1 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-CI M12FS-5CON 18,5 VPE1000 - Contact carrier



1545399

<https://www.phoenixcontact.com/us/products/1545399>

Technical data

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Number of positions | 5 |
| Thread type | M12 |

Environmental and real-life conditions

Ambient conditions

| | |
|----------------|--------------------------|
| UL Type Rating | Type 4 (indoor use only) |
|----------------|--------------------------|

SACC-CI M12FS-5CON 18,5 VPE1000 - Contact carrier





1545399


<https://www.phoenixcontact.com/us/products/1545399>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1545399>

|  cULus Recognized Approval ID: E221474-20140616 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 60 V | 4 A | - | - |

|  UL Recognized Approval ID: E118976 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 60 V | 4 A | - | - |

|  cUL Recognized Approval ID: E118976 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 60 V | 4 A | - | - |

SACC-CI M12FS-5CON 18,5 VPE1000 - Contact carrier



1545399

<https://www.phoenixcontact.com/us/products/1545399>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440223 |
| ECLASS-15.0 | 27440223 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003557 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121421 |
|-------------|----------|

SACC-CI M12FS-5CON 18,5 VPE1000 - Contact carrier



1545399

<https://www.phoenixcontact.com/us/products/1545399>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.067 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com