

# SAC-4P-M12MS CCL TR - Termination resistor



1558470

<https://www.phoenixcontact.com/us/products/1558470>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CC-Link termination resistor, 4-pos., M12 plug



## Commercial data

Item number	1558470
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF10
Product key	AF1GVX
GTIN	4046356293648
Weight per piece (including packing)	16.9 g
Weight per piece (excluding packing)	11.26 g
Customs tariff number	85332100
Country of origin	DE

# SAC-4P-M12MS CCL TR - Termination resistor



1558470

<https://www.phoenixcontact.com/us/products/1558470>

## Technical data

### Product properties

Product type	Terminal resistor
Number of positions	4
Coding	A

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	24 V AC
	24 V DC
Nominal current $I_N$	20 mA

### General

Termination resistor	110 $\Omega$ (Contact 2 and 4)
Power consumption	0.5 W

### Signaling

Status display	no
Status display present	no

### Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

### Connector

#### Connection 1

Type	Plug straight M12
Coding type	A

#### Connection 2

Type	free cable end
------	----------------

### Mechanical properties

#### Mechanical data

# SAC-4P-M12MS CCL TR - Termination resistor



1558470

<https://www.phoenixcontact.com/us/products/1558470>

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C

# SAC-4P-M12MS CCL TR - Termination resistor




1558470

<https://www.phoenixcontact.com/us/products/1558470>

## Drawings

Dimensional drawing



M12 termination resistor

# SAC-4P-M12MS CCL TR - Termination resistor

1558470


<https://www.phoenixcontact.com/us/products/1558470>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

Circuit diagram



CC-Link termination resistor, R = 110 Ω

# SAC-4P-M12MS CCL TR - Termination resistor



1558470

<https://www.phoenixcontact.com/us/products/1558470>

## Classifications

### ECLASS

ECLASS-13.0	19070403
ECLASS-15.0	19070403

### ETIM

ETIM 10.0	EC000448
-----------	----------

### UNSPSC

UNSPSC 21.0	32121600
-------------	----------

# SAC-4P-M12MS CCL TR - Termination resistor



1558470

<https://www.phoenixcontact.com/us/products/1558470>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.277 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)