

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1629212

The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable connection solutions in the industrial environment
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1619472 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAEB |
| GTIN | 4046356823753 |
| Weight per piece (including packing) | 96.5 g |
| Weight per piece (excluding packing) | 90.228 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Order crimp contacts Ø 1 mm separately |
| Order information: | When using a specific cable with Ø 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786600) |

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts Ø 1 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Connection method | Crimp connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 12 |
| Direction of rotation | Standard |
| Connection profile | 12 |
| Number (Signal contacts) | 12 |
| Contact diameter (Signal contacts) | 1 mm |
| Litz wires Min. cross section (Signal contacts) | 0.06 mm ² |
| Litz wires Max. cross section (Signal contacts) | 1 mm ² |
| Rated current Contact (Signal contacts) | 8 A (for max. connection cross section) |
| Rated voltage Contact (Signal contacts) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |

Housing

| | |
|-----------------------------------|-------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | SPEEDCON |
| Pg screw connection | none |
| Housing material | Metal |
| Degree of protection (plugged in) | IP67 |

Seal

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

| | |
|-------------------------|------------------|
| External cable diameter | 3 mm ... 14.5 mm |
| Seal material | FPM |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), standard socket

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619472>

|  cUL Recognized Approval ID: E335019-20141210 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 6 A | 18 | - |

|  UL Recognized Approval ID: E335019-20141210 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 48 V | 8 A | 18 | - |

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-12F1N8A85DUS - Cable connector



1619472

<https://www.phoenixcontact.com/us/products/1619472>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com