

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1069313

The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

## Commercial data

Item number	1621434
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEA
GTIN	4046356932516
Weight per piece (including packing)	93.2 g
Weight per piece (excluding packing)	86.89 g
Customs tariff number	85366990
Country of origin	DE

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

## Technical data

### Notes

Order information:	Order crimp contacts separately
Order information:	When using a specific cable with $\varnothing$ 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786601)

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

Direction of rotation	Counter direction
-----------------------	-------------------

### Insulating body

Note	Order information: Order crimp contacts $\varnothing$ 1 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

### Seal

External cable diameter	3 mm ... 14.5 mm
-------------------------	------------------

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

Seal material	NBR
---------------	-----

## Environmental and real-life conditions

### Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %
--	---------------

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

## Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), socket counter direction

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1621434>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	48 V	4 A	20	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	48 V	6 A	20	-

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-12S2N8A80DN - Cable connector



1621434

<https://www.phoenixcontact.com/us/products/1621434>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5c3c47b1-bd47-4fd5-9fb0-89e73ef5daee

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)