

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Plastic, connection method: Insulation displacement connection, connection cross section: AWG 26- 23, cable outlet: straight, color: black, Ethernet

Your advantages

- Easy and time-saving assembly with IDC fast connection technology
- Can be used internationally due to EAC, UL 1863, and CAN/CSA C22.2
- Ideal companion for servicing or repairs in the field: no special tools required for mounting

Commercial data

Item number	1658008
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNAAD
GTIN	4046356138536
Weight per piece (including packing)	10.38 g
Weight per piece (excluding packing)	9.012 g
Customs tariff number	85366990
Country of origin	CH

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight
Positions/contacts	8P8C

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	330 kV
Rated current	1.75 A
Contact resistance	< 20 m Ω (Contact) < 100 m Ω (shield)
Frequency range	100 MHz
Insulation resistance	> 500 M Ω
Nominal voltage U_N	48 V
Nominal current I_N	1.75 A
Contact resistance per contact pair	< 20 Ω
Contact resistance	> 10 m Ω (Wire – IDC) 0.005 Ω (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps
Power transmission	PoE++ in accordance with: IEEE 802.3bt

Connection data

Connection technology

Connection method	Insulation displacement connection
Connection cross section AWG	26 ... 23 (solid) 26 ... 23 (flexible)
Conductor cross-section	0.14 mm ² ... 0.25 mm ² (solid) 0.14 mm ² ... 0.25 mm ² (flexible)
Connection in acc. with standard	in accordance with IEC 60603-7-1

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Cable outlet, angle	180
---------------------	-----

Interfaces

Signal type/category	Ethernet CAT5, 1 Gbps
----------------------	-----------------------

Dimensions

Width	14 mm
Height	14.6 mm
Length	55.85 mm

Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Housing material	Plastic
Cable seal material	NBR
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	FPM
Locking latch material	PC
Material for screw connection	PA

Cable/line

Signal type/category	Ethernet CAT5, 1 Gbps
External cable diameter	4.5 mm ... 8 mm
External cable diameter	4.5 mm ... 8 mm
Cable cross section	0.14 mm ²
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500.00 V
Halogen-free	no

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Test specification

Type of test	Vibration test
Specification	IEC 60068-2-6
Frequency	10-500 Hz
Sweep speed	1 octave/min

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Mounting

Mounting type	For field assembly
---------------	--------------------

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector

1658008

<https://www.phoenixcontact.com/us/products/1658008>



Drawings

Schematic diagram



Connector pin assignment

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1658008>



UL Listed

Approval ID: FILE E 335024



cUL Listed

Approval ID: FILE E 335024

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Classifications

ECLASS

ECLASS-13.0	27440114
ECLASS-15.0	27440114

ETIM

ETIM 10.0	EC002636
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-08-RJ45-5-Q/IP20 BK - RJ45 connector



1658008

<https://www.phoenixcontact.com/us/products/1658008>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	14622286-2cb4-46e5-9715-6fce15f91571

EF3.1 Climate Change

CO2e kg	0.816 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com