

# UM-ALU 4-72 FRONT 200 - Front plate



2200930

<https://www.phoenixcontact.com/us/products/2200930>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Basic profile front plate, width: 71.8 mm, length: 201.3 mm, depth: 2 mm, recommended for UM-ALU 4-..COVER PA.. lateral elements



## Your advantages

- Aluminum extruded profile
- Variety of connection technology
- Can be mounted on the DIN rail
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- EMC protection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2200930       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC14          |
| Product key                          | ACHDFC        |
| GTIN                                 | 4046356720465 |
| Weight per piece (including packing) | 80.4 g        |
| Weight per piece (excluding packing) | 80.4 g        |
| Customs tariff number                | 76061191      |
| Country of origin                    | DE            |

# UM-ALU 4-72 FRONT 200 - Front plate



2200930

<https://www.phoenixcontact.com/us/products/2200930>

## Technical data

### Product properties

|                              |                              |
|------------------------------|------------------------------|
| Product type                 | Component housing cover      |
| Housing type                 | Press-drawn section housings |
| Housing series               | UM-ALU                       |
| Product family               | UM-ALU 4-72                  |
| Ventilation openings present | no                           |

### Dimensions

|        |          |
|--------|----------|
| Width  | 71.8 mm  |
| Depth  | 2 mm     |
| Length | 201.3 mm |

### Material specifications

|                         |                     |
|-------------------------|---------------------|
| Color (Housing)         | aluminum color      |
| Material Housing        | Aluminum (anodized) |
| Surface characteristics | anodized            |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP40   |
| Ambient temperature (operation)         | -40 °C ... 100 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |

# UM-ALU 4-72 FRONT 200 - Front plate


2200930

<https://www.phoenixcontact.com/us/products/2200930>



## Drawings

Schematic diagram



# UM-ALU 4-72 FRONT 200 - Front plate



2200930

<https://www.phoenixcontact.com/us/products/2200930>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# UM-ALU 4-72 FRONT 200 - Front plate



2200930

<https://www.phoenixcontact.com/us/products/2200930>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)