

# HSC-LR 7U KIT 2003 - Locking

2201795

<https://www.phoenixcontact.com/us/products/2201795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, 7U, Lock and Release system, width: 16.1 mm, height: 89.95 mm, depth: 8.8 mm, color: orange (similar RAL 2003)

## Your advantages

- Easy, tool-free mounting
- Lock and Release interlock in contrasting color for intuitive operation
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2201795       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AC15          |
| Product key                          | ACHECZ        |
| GTIN                                 | 4046356933582 |
| Weight per piece (including packing) | 5.18 g        |
| Weight per piece (excluding packing) | 5.18 g        |
| Customs tariff number                | 85389099      |
| Country of origin                    | DE            |

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

### Product properties

|                |                   |
|----------------|-------------------|
| Product type   | Mounting material |
| Housing type   | DIN rail housing  |
| Housing series | ME-IO             |
| Product family | ME-IO             |

### Dimensions

|        |          |
|--------|----------|
| Width  | 16.1 mm  |
| Height | 89.95 mm |
| Depth  | 8.8 mm   |

### Material specifications

|  |                   |
|--|-------------------|
| Color                                  | orange (RAL 2003) |
| Material                               | PA6-GF30          |
| Flammability rating according to UL 94 | V0                |
| Surface characteristics                | untreated         |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

### Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

# HSC-LR 7U KIT 2003 - Locking



2201795

<https://www.phoenixcontact.com/us/products/2201795>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201795>



**UL Recognized**

Approval ID: E240868

# HSC-LR 7U KIT 2003 - Locking



2201795

<https://www.phoenixcontact.com/us/products/2201795>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HSC-LR 7U KIT 2003 - Locking



2201795

<https://www.phoenixcontact.com/us/products/2201795>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.039 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)