

HCS-C MAXI 1W C 1 1 7035 - Electronics housing



2203167

<https://www.phoenixcontact.com/us/products/2203167>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Handheld housing, C-Maxi, light gray, consisting of two half shells, two front plates with screws, front 1.1 mm recessed, with window and keypad slot

Your advantages

- Suitable for handheld devices
- Easy integration of LCD displays and membrane keypads
- Ergonomic straight or staggered housing design
- Fast mounting, thanks to the modular design

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2203167 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC02 |
| Product key | ACFACA |
| GTIN | 4055626377223 |
| Weight per piece (including packing) | 204.5 g |
| Weight per piece (excluding packing) | 204.5 g |
| Customs tariff number | 84879090 |
| Country of origin | DE |

2203167

<https://www.phoenixcontact.com/us/products/2203167>

Technical data


Product properties

| | |
|------------------------------|------------------|
| Product type | Complete housing |
| Housing type | Handheld housing |
| Housing type | Handheld housing |
| Housing series | HCS |
| Ventilation openings present | no |
| Battery compartment | no |

Display

| | |
|----------|-------------------------------------|
| Diagonal | 2.8 in. / 7 cm (Window for display) |
|----------|-------------------------------------|

Dimensions

| | |
|----------------------|---|
| Dimensional drawing |  |
| Width | 94 mm |
| Height | 182.5 mm |
| Depth | 39 mm |
| Dimensions | 73 mm x 80 mm x 1.1 mm (Recessed area on front) |
| | 73 mm x 7.9 mm x 1.1 mm (Recessed area on front) |
| | 73 mm x 8 mm x 1.1 mm (Recessed area on front) |
| | 62 mm x 33 mm (Window for display) |
| | 73 mm x 44 mm x 2.7 mm (Holder for cover lens) |
| Front with faceplate | top, 1 x (73.8 mm x 25.8 mm) |
| | bottom, 1 x (73.8 mm x 25.8 mm) |

PCB design

| | |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material Housing | ABS |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 400 ≤ CTI < 600 |
| Insulating material | II |
| Surface characteristics | untreated |

Environmental and real-life conditions

Glow-wire test

HCS-C MAXI 1W C 1 1 7035 - Electronics housing



2203167

<https://www.phoenixcontact.com/us/products/2203167>

| | |
|------------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 80 °C |
| Test duration | 1 h |
| Force | 20 |

Ambient conditions

| | |
|---|---|
| Max. IP code to attain | IP54 |
| Ambient temperature (operation) | -40 °C ... 80 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 80 °C |
| Relative humidity (storage/transport) | 95 % |

PCB data

| | |
|-----------------------|-------------------|
| Number of PCB holders | 3 |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

Mounting

| | |
|---------------------------|---|
| Tightening torque / speed | Screw connection between housing halves: 0.25 - 0.3 Nm / 500 - 1000 rpm |
|---------------------------|---|

2203167

<https://www.phoenixcontact.com/us/products/2203167>

Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center

2203167

<https://www.phoenixcontact.com/us/products/2203167>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190102 |
| ECLASS-15.0 | 27190102 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001031 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HCS-C MAXI 1W C 1 1 7035 - Electronics housing



2203167

<https://www.phoenixcontact.com/us/products/2203167>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com