

# PLC-VT - Feed-through terminal block



2296870

<https://www.phoenixcontact.com/us/products/2296870>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE feed-through terminal block (2-conductor screw connection), for PLC-INTERFACE universal series

## Your advantages

- Can be combined with PLC-INTERFACE universal series
- With LED as an option
- Signal path with additional potential level for free assignment (2-conductor connection)

## Commercial data

Item number	2296870
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C421
Product key	DK21D6
GTIN	4017918821609
Weight per piece (including packing)	34.02 g
Weight per piece (excluding packing)	27.6 g
Customs tariff number	85369010
Country of origin	DE

# PLC-VT - Feed-through terminal block



2296870

<https://www.phoenixcontact.com/us/products/2296870>

## Technical data

### Notes

Notes on operation	The necessary requirements for insulation (basic insulation or reinforced insulation) from adjacent modules (in DIN-rail direction) must be realized by applying suitable measures (e. g., partition plates).
Notes on operation	Ensure that the supply voltage of the device has a common reference potential.
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

### Product properties

Product type	Feed-through terminal block
Product family	PLC-INTERFACE

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	III
Pollution degree	2

### Electrical properties

Operating voltage (AC/DC)	250 V AC/DC
Current (per branch)	≤ 6 A
Current (per connection terminal block with bridge shaft)	≤ 6 A

#### Air clearances and creepage distances

Rated insulation voltage	300 V
Rated surge voltage	4 kV

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	5
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Signaling

Status display present	no
------------------------	----

### Dimensions

#### Item dimensions

# PLC-VT - Feed-through terminal block



2296870

<https://www.phoenixcontact.com/us/products/2296870>

Width	6.2 mm
Height	80 mm
Depth	94 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UKCA

Certificate	UKCA-compliant
-------------	----------------

### Shipbuilding approval

Certificate	TAE0000196
-------------	------------

### Shipbuilding data

Temperature	D
Humidity	A
Vibration	B/C
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# PLC-VT - Feed-through terminal block




2296870

<https://www.phoenixcontact.com/us/products/2296870>

## Drawings

Circuit diagram



PLC-VT connection scheme

# PLC-VT - Feed-through terminal block





2296870


<https://www.phoenixcontact.com/us/products/2296870>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2296870>

 <b>cUL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	220 V	6 A	-	-

 <b>UL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	220 V	6 A	-	-

 <b>EAC</b> Approval ID: RU*DE.*09.B.00387/20	
---	--

 <b>DNV GL</b> Approval ID: TAE0000196	
--	--

# PLC-VT - Feed-through terminal block



2296870

<https://www.phoenixcontact.com/us/products/2296870>

## Classifications

### ECLASS

ECLASS-13.0	27371692
ECLASS-15.0	27371692

### ETIM

ETIM 10.0	EC002586
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# PLC-VT - Feed-through terminal block



2296870

<https://www.phoenixcontact.com/us/products/2296870>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)