

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FL COMSERVER WLAN..., to convert a serial RS-232/422/485 or USB interface to 54 Mbps WLAN Ethernet, supports TCP, UDP applications, incl. CD-ROM with Com Port Redirector Software and user documentation (PDF).

Your advantages

- 3-way electrical isolation VCC // RS-232/RS-422/RS-485 // network
- Extended temperature range of -25°C to +60°C
- Ad-hoc or infrastructure mode
- LED diagnostic indicators
- Simple configuration software
- Redundant power supply and modular station structure with TBUS connectors
- Software for virtual COM ports supplied as standard

Commercial data

Item number	2313559
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN26
Product key	DNC671
GTIN	4046356480109
Weight per piece (including packing)	232.8 g
Weight per piece (excluding packing)	232.8 g
Customs tariff number	85176200
Country of origin	DE

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Technical data

Product properties

Product type	Interface converter
MTTF	2120 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	851 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	346 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
MTBF	1153 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	262 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

Functions

Management	Web-based management
	SNMP v1/v2

Electrical properties

Electrical isolation	VCC // WLAN, RS-232, RS-422, RS-485, USB
Maximum power dissipation for nominal condition	2.4 W
Test voltage data interface/data interface	1.5 kV _{rms} (50 Hz, 1 min.)
Test voltage data interface/power supply	1.5 kV _{rms} (50 Hz, 1 min.)
	1.5 kV _{rms}

Supply

Supply voltage range	10 V DC ... 30 V DC (via pluggable COMBICON screw terminal block)
	19 V AC ... 29 V AC (via pluggable COMBICON screw terminal block)
Nominal supply voltage	24 V DC ±20 % (as an alternative or redundant, via backplane bus contact and system current supply)
Typical current consumption	≤ 100 mA (24 V DC)

Function

Management	With configuration software via USB and serial interface
Status and diagnostic indicators	LEDs: UL (logic voltage), TD + RD (data activity serial), 4-level bar graph (received wireless power), SER ERR (serial errors)

Connection data

Supply

Tightening torque	0.56 Nm ... 0.79 Nm
-------------------	---------------------

Interfaces

Signal	Ethernet
--------	----------

Data: V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Serial transmission speed	0.3; 1.2; 2.4; 4.8; 7.2; 9.6; 19.2; 31.25; 38.4; 57.6; 75; 93.75; 115.2 kbps
Connection method	D-SUB 9 plug
File format/coding	Serial asynchronous UART/NRZ, 7/8 data, 1/2 stop, 1 parity, 10/11-bit character length
Data flow control/protocols	Software handshake, Xon/Xoff or hardware handshake RTS/CTS

Data: RS-422 interface in acc. with ITU-T V.11, EIA/TIA-422, DIN 66348-1

Serial transmission speed	0.3; 1.2; 2.4; 4.8; 7.2; 9.6; 19.2; 31.25; 38.4; 57.6; 75; 93.75; 115.2; 136; 187.5 kbps
Connection method	Plug-in/screw connection via COMBICON
Transmission length	≤ 1200 m
Termination resistor	390 Ω 180 Ω 390 Ω (Can be connected)
File format/coding	Serial asynchronous UART/NRZ, 7/8 data, 1/2 stop, 1 parity, 10/11-bit character length
Data flow control/protocols	Automatic control

Data: RS-485 interface, in acc. with EIA/TIA-485, DIN 66259-4/RS-485 2-wire

Serial transmission speed	0.3; 1.2; 2.4; 4.8; 7.2; 9.6; 19.2; 31.25; 38.4; 57.6; 75; 93.75; 115.2; 136; 187.5 kbps
Connection method	Plug-in/screw connection via COMBICON
Termination resistor	390 Ω 180 Ω 390 Ω (Can be connected)
File format/coding	Serial asynchronous UART/NRZ, 7/8 data, 1/2 stop, 1 parity, 10/11-bit character length
Data flow control/protocols	Automatic control

Data: USB interface

Connection method	Mini-USB B, socket
-------------------	--------------------

Wireless

Interface description	WLAN as per IEEE 802.11 b/g
Operating mode	Infrastructure mode, ad-hoc mode
Frequency range	2.402 GHz ... 2.48 GHz (ISM bandwidth)
Transmit capacity, minimum	-28 dBm (can be set via software)
Transmit capacity, maximum	20 dBm (can be set via software)
Data rate	≤ 54 Mbps
Minimum receiver sensitivity	-85 dBm
Antenna	External
Connection method	SMA socket
Security	802.11i, WPA PSK (preshared key), WPA2 PSK, AES, WEP 64 Bit/128 Bit, TKIP
Configuration	USB, serially with configuration software
Protocols supported	TCP/IP, UDP

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Dimensions

Width	22.5 mm
Height	99 mm
Depth	121 mm

Material specifications

Color	green
Material (Housing)	PA 6.6-FR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	508 Listed
----------------	------------

Wireless approval USA, FCC

Note	Part 15, RSS 210
------	------------------

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-6-2:2005

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Classifications

UNSPSC

UNSPSC 21.0	43222604
-------------	----------

FL COMSERVER WLAN 232/422/485 - Interface converters



2313559

<https://www.phoenixcontact.com/us/products/2313559>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com