

# UM 45-MKDS/MDSTBW/ 8SI/SO262 - Termination board



2319443

<https://www.phoenixcontact.com/us/products/2319443>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse module, with screw connection, COMBICON connectors with stand-off and encoding against incorrect connection, for mounting on NS 35/7,5 or NS 32

## Commercial data

Item number	2319443
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2A88
GTIN	4046356364898
Weight per piece (including packing)	295.4 g
Weight per piece (excluding packing)	245 g
Customs tariff number	85369010
Country of origin	DE

# UM 45-MKDS/MDSTBW/ 8SI/SO262 - Termination board



2319443

<https://www.phoenixcontact.com/us/products/2319443>

## Technical data

### Product properties

Product type	Interface module
--------------	------------------

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	III
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	230 V AC
Max. current carrying capacity per branch	2 A

#### Air clearances and creepage distances

Rated insulation voltage	230 V
Rated surge voltage	4 kV (1.2/50 $\mu$ s)

### Connection data

#### PCB connection

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of positions	8
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

#### COMBICON connection

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Dimensions

#### Item dimensions

Width	48.5 mm
Height	45 mm
Depth	160 mm

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)

# UM 45-MKDS/MDSTBW/ 8SI/SO262 - Termination board



2319443

<https://www.phoenixcontact.com/us/products/2319443>

Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	max. 2000 m

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# UM 45-MKDS/MDSTBW/ 8SI/SO262 - Termination board



2319443

<https://www.phoenixcontact.com/us/products/2319443>

## Classifications

### ECLASS

ECLASS-13.0

27141152

### ETIM

ETIM 9.0

EC002780

### UNSPSC

UNSPSC 21.0

39121400

# UM 45-MKDS/MDSTBW/ 8SI/SO262 - Termination board



2319443

<https://www.phoenixcontact.com/us/products/2319443>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)