

TP 3154W - Touch panel



2402631

<https://www.phoenixcontact.com/us/products/2402631>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel, 39.12 cm / 15.4"-TFT display (analog resistive (polyester)), 1280 x 800 pixel(s) (WXGA), 65536 colors, Arm® Cortex®-A8, 800 MHz, 2x USB Host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7, Visu+ / AX OPC Server, without bus system.

Commercial data

Item number	2402631
Packing unit	1 pc
Sales key	DR17
Product key	DRCABC
GTIN	4055626246406
Weight per piece (including packing)	1,900 g
Weight per piece (excluding packing)	1,900 g
Customs tariff number	84714100
Country of origin	DE

TP 3154W - Touch panel



2402631

<https://www.phoenixcontact.com/us/products/2402631>

Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
RAM	512 MB RAM
Data storage system	Flash, 1 GB
Slots	1x SD

Display

Display type	39.12 cm / 15.4"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	360 cd/m ² typical (adjustable)
MTBF	50000 h
Color spectrum	65536 colors
Reading angle left	80.00 °
Reading angle right	80.00 °
Reading angle top	70.00 °
Reading angle bottom	70.00 °

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without bus system

System properties

User software	Visu+ AX OPC Server
---------------	------------------------

System requirements

Runtime system	Visu+ Runtime
----------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Power supply unit	24 V DC ±20 %
Typical current consumption	0.9 A

TP 3154W - Touch panel



2402631

<https://www.phoenixcontact.com/us/products/2402631>

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Supply

Power consumption	typ. 21.6 W
-------------------	-------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Altitude	3000 m
Permissible humidity (operation)	20 % ... 85 %
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	420 mm / 297 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	396 mm / 273 mm / 64 mm (Installation cutout)
-------------------------------------	---

TP 3154W - Touch panel

2402631

<https://www.phoenixcontact.com/us/products/2402631>



Classifications

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

TP 3154W - Touch panel



2402631

<https://www.phoenixcontact.com/us/products/2402631>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(b), 6(b)-II, 6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c6ee7355-7e9d-4385-a4c7-2c7b7eb1d7fc

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com