

## Optical element - PSD-S OE LED BL BU - 2700132

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




LED blinking light element, 24 V AC/DC, blue

### Your advantages

- ✓ Tool-free element changeover
- ✓ High light and color intensity
- ✓ Can be freely combined
- ✓ Minimum LED service life of 50,000 h
- ✓ Low power consumption
- ✓ Degree of protection: IP65



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 491259
GTIN	4046356491259

### Technical data

#### Dimensions

Diameter	70 mm
Height	65.5 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Degree of protection	IP65, when installed or with cover

#### General

Material	Polycarbonate PC
Calotte color	blue
Weight	59 g

# Optical element - PSD-S OE LED BL BU - 2700132

## Technical data

### General

Mounting position	any
Assembly instructions	Rubber seal pre-installed for each element

### Electrical data

Input voltage	24 V AC/DC
Maximum inrush current	max. 500 mA
Current consumption	25 mA
Service life, electrical	max. 100,000 h
Operating time	100 %
Optical signal type	LED flashlight
Signal frequency	approx. 1 Hz

### Approvals / conformities

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	27371220
eCl@ss 11.0	27371220
eCl@ss 4.0	27143200
eCl@ss 4.1	27143200
eCl@ss 5.0	27371200
eCl@ss 5.1	27371200
eCl@ss 6.0	27371200
eCl@ss 7.0	27371220
eCl@ss 9.0	27371220

### ETIM

ETIM 3.0	EC000232
ETIM 4.0	EC000232
ETIM 6.0	EC000232
ETIM 7.0	EC000232

### UNSPSC

UNSPSC 6.01	43172015
-------------	----------

# Optical element - PSD-S OE LED BL BU - 2700132

## Classifications

### UNSPSC

UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	46171604
UNSPSC 18.0	46171604
UNSPSC 19.0	46171604
UNSPSC 20.0	46171604
UNSPSC 21.0	46171604

## Approvals






### Approvals

#### Approvals

UL Listed / cUL Listed / EAC / EAC-RoHS / EAC / cULus Listed

#### Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 123528
cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 123528
EAC			RU *- DE.A*30.B.00237
EAC-RoHS			RU D- DE.HB35.B.00391
EAC			EAC-Zulassung

## Optical element - PSD-S OE LED BL BU - 2700132

### Approvals

cULus Listed



Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>