

Communication module - NLC-COM-ENET-MB1 - 2701124

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet communication module. Allows the Nanoline controller to be connected to an Ethernet, operating as a Modbus TCP Server.

Product Description

Adds Ethernet connectivity (Modbus TCP Server functionality) to Nanoline controller. Attaches to left-side of base unit.

Your advantages

- Enables all I/O points, registers, timers, counters, program flags, and system flags to be read and written remotely
- Password control can limit access (read-only or read/write)
- Watchdog timer monitors communication, providing either a warning or fault
- Connects to an Ethernet network to function as a Modbus TCP client



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356325295

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C

Communication module - NLC-COM-ENET-MB1 - 2701124

Technical data

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	90 %

Interfaces

Interface	Ethernet 10/100Base T
Connection method	RJ45
Transmission speed	10/100 Mbps (auto negotiation)
Transmission length	100 m
Signal LEDs	LNK/ACT; Module; Network

Supply


Power supply connection	Screw connection
Supply voltage	24 V DC (Power available via logic module)
Max. current consumption	180 mA (at 18 V DC)
Typical current consumption	110 mA

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27242216
eCl@ss 11.0	27242216
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27242700
eCl@ss 5.1	27242700
eCl@ss 6.0	27242200

Communication module - NLC-COM-ENET-MB1 - 2701124

Classifications

eCl@ss

eCl@ss 7.0	27242216
eCl@ss 9.0	27242216

ETIM

ETIM 2.0	EC001417
ETIM 3.0	EC001417
ETIM 4.0	EC001417
ETIM 6.0	EC001417
ETIM 7.0	EC001417

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39122329
UNSPSC 18.0	39122329
UNSPSC 19.0	39122329
UNSPSC 20.0	39122329
UNSPSC 21.0	39122329

Approvals

Approvals

Approvals

UL Listed / EAC / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

EAC		EAC-Zulassung
-----	--	---------------

Communication module - NLC-COM-ENET-MB1 - 2701124

Approvals

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	---	---	---------------

cULus Listed			
--------------	---	--	--

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>