

PC WORX SRT - Controller



2701680

<https://www.phoenixcontact.com/us/products/2701680>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



This software PLC enables your PC to now handle all control tasks. Control your processes as required via PROFINET or Modbus/TCP

Your advantages

- Integrated web server for visualization with WebVisit
- OPC support using an AX OPC server
- FTP server
- Easy installation on Valueline industrial PCs
- Numerous protocols supported such as: HTTP, FTP, SNMP, SMTP, SQL, MySQL, etc.
- Integrated PROFINET controller and PROFINET device
- Engineering with PC Worx (IEC 61131-3)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2701680 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DR10 |
| Product key | DRABAA |
| GTIN | 4046356779760 |
| Weight per piece (including packing) | 78.4 g |
| Weight per piece (excluding packing) | 78.4 g |
| Customs tariff number | 85234910 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | Software PLC |
|--------------|--------------|

System properties

| | |
|--------------------|--------------------------------|
| Performance class | Small-scale controller |
| Programmable under | PC Worx in IEC 61131 |
| Application type | distributed control technology |

IEC 61131 runtime system

| | |
|----------------------------|--|
| Program memory | 1 Mbyte |
| Data storage system | 1 Mbyte |
| Retentive data storage | 48 kByte |
| Number of control tasks | 8 |
| Number of data blocks | depending on data storage |
| Number of timers, counters | depending on data storage |
| Processing speed | 5.5 μ s (1 K mixed instructions, Intel® Atom™ Z510PT) 4 μ s (1 K bit instructions, Intel® Atom™ Z510PT) |

PROFINET

| | |
|-----------------|--------------------------------------|
| Device function | PROFINET controller, PROFINET device |
|-----------------|--------------------------------------|

Functionality

| | |
|-----------------|---|
| Basic functions | Complete PLC Non-realtime-capable software PLC for installation on a standard PC with integrated Modbus/TCP, plus PROFINET-Controller and device functionality |
|-----------------|---|

System requirements

| | |
|---------------------|---|
| Operating equipment | Keyboard, mouse recommended |
| Operating system | Windows® 7 (32-Bit/64-Bit) Windows® 8.1 (32-Bit/64-Bit) Windows® Embedded Standard 7 Windows® Embedded 2009 Windows® 10 (32-Bit/64-Bit) |
| Processor | min. Intel® Atom™ |
| Hard disk memory | min. 1 GByte |
| Interfaces | Ethernet Port |
| Supported browsers | Internet Explorer Version 8 or later |
| Screen resolution | XGA (1024 x 768) |

Electrical properties

Real-time clock

| | |
|----------------|-----|
| Realtime clock | yes |
|----------------|-----|

PC WORX SRT - Controller

2701680

<https://www.phoenixcontact.com/us/products/2701680>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242501 |
| ECLASS-15.0 | 27242501 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002537 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43233600 |
|-------------|----------|

PC WORX SRT - Controller



2701680

<https://www.phoenixcontact.com/us/products/2701680>

Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|---|---|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.104 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com