

# FL SFP FE WDM20-A - Media module



2702437

<https://www.phoenixcontact.com/us/products/2702437>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fast Ethernet SFP WDM module for transmission up to a maximum of 20 km on a single fiber with a wavelength of 1310/1550 nm.

## Product description

SFP WDM module with a data transmission speed of 100 Mbps, a wavelength of 1310/1550 nm, and a maximum transmission length of 20 km.

## Your advantages

- MSA compliant

## Commercial data

Item number	2702437
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN1ZS
GTIN	4055626189031
Weight per piece (including packing)	33 g
Weight per piece (excluding packing)	33 g
Customs tariff number	85176200
Country of origin	TW

# FL SFP FE WDM20-A - Media module



2702437

<https://www.phoenixcontact.com/us/products/2702437>

## Technical data

### Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Housing material	Metal
------------------	-------

### Mounting

Mounting type	Plug-in mounting
Mounting type	Insert in SFP slot

### Interfaces

Ethernet FO

Connection method	LC
Transmission speed	100 Mbps
Transmit capacity, minimum	-14 dBm
Transmit capacity, maximum	-8 dBm
Minimum receiver sensitivity	-32 dBm
Maximum receiver sensitivity	-3 dBm
Transmission physics	Single-mode fiberglass
Transmission length	20 km (Fiberglass 9/125)
Wavelength	1310 nm (TX) 1550 nm (RX)
Signal LEDs	depending on the Factoryline device
No. of channels	1 (LC single mode)

### Product properties

Product type	SFP module
Type	Factoryline devices with SFP slot
MTTF	201 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1)
Format	SFP (Small Form-factor Pluggable)

### Signaling

Status display	via a Factoryline device
----------------	--------------------------

2702437

<https://www.phoenixcontact.com/us/products/2702437>

## Electrical properties

Current consumption	300 mA
Maximum power dissipation for nominal condition	1 W
Transmission medium	FO

## Supply

Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot
Max. current consumption	300 mA
Current consumption	300 mA

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Case temperature	max. 85 °C (Operation)

## Standards and regulations

Standard designation	Laser equipment safety
Standards/specifications	IEC 60825

# FL SFP FE WDM20-A - Media module



2702437

<https://www.phoenixcontact.com/us/products/2702437>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2702437>



**DNV GL**

Approval ID: TAA00000YV



**LR**

Approval ID: LR22250919TA



**NK**

Approval ID: TA24215M



**BV**

Approval ID: 48146\_B1 BV

**BSH**

Approval ID: Nr. 966



**RINA**

Approval ID: ELE014724XG001

**ABS**

Approval ID: 21\_2066186\_1\_PDA

# FL SFP FE WDM20-A - Media module



2702437

<https://www.phoenixcontact.com/us/products/2702437>

## Classifications

### ECLASS

ECLASS-13.0

19179090

### ETIM

ETIM 9.0

EC000310

### UNSPSC

UNSPSC 21.0

43222600

# FL SFP FE WDM20-A - Media module



2702437

<https://www.phoenixcontact.com/us/products/2702437>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)