

# SYS N4 480D - Surge protection device



2800707

<https://www.phoenixcontact.com/us/products/2800707>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Combination lightning current arrester and TVSS system for ungrounded 480 V Delta systems



## Product description

Combination lightning current arrester and TVSS for 480 V Delta. Components are housed in an IP66/NEMA 4 cabinet.

## Commercial data

Item number	2800707
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL01
Product key	CL1621
GTIN	4046356642934
Weight per piece (including packing)	222.22 g
Weight per piece (excluding packing)	222.22 g
Customs tariff number	85363090
Country of origin	DE

# SYS N4 480D - Surge protection device



2800707

<https://www.phoenixcontact.com/us/products/2800707>

## Technical data

### Product properties

Product type	Surge protection for NEMA power supply units
IEC test classification	I + II
EN type	T1
Type	Housing for surface mounting
Surge protection fault message	Remote indication contact

### Electrical properties

Nominal voltage $U_N$	< 480 V
Fuse	200 kA VSP100, 100 A, 200 kAIC (IR)

### General

Power Systems	480 V Delta
---------------	-------------

### Connection data

Conductor cross-section flexible min.	16 mm <sup>2</sup>
Conductor cross-section flexible max.	35 mm <sup>2</sup>
Conductor cross-section, rigid min.	10 mm <sup>2</sup>
Conductor cross-section, rigid max.	50 mm <sup>2</sup>
Connection method	Screw connection
Conductor cross-section flexible min.	0.14 mm <sup>2</sup>
Conductor cross-section flexible max.	1.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.14 mm <sup>2</sup>
Conductor cross-section, rigid max.	1.5 mm <sup>2</sup>

### Dimensions

Width	400 mm
Height	500 mm
Depth	210 mm

### Material specifications

Housing material	Steel
------------------	-------

### Protective circuit

Nominal voltage $U_N$	480 V AC (Delta)
Maximum continuous operating voltage $U_C$ (L-L)	600 V AC
Maximum continuous operating voltage $U_C$ (L-PE)	480 V AC
Follow current interrupt rating $I_{fi}$	50 kA
Response time $t_A$	≤ 25 ns

### Environmental and real-life conditions

#### Ambient conditions

# SYS N4 480D - Surge protection device



2800707

<https://www.phoenixcontact.com/us/products/2800707>

Degree of protection	IP66/NEMA 4
Ambient temperature (operation)	-40 °C ... 80 °C

## Approvals

### UL specifications

Short-circuit current rating (SCCR)	50 kA
UL type	type 2
Nominal discharge current $I_n$	20 kA
Maximum Surge Current per Phase	50 kA
Nominal voltage	480 V AC (Delta)
Power distribution system	Delta

## Standards and regulations

### Standards

Standards/regulations	ANSI/UL 1449:2014 Ed.4+R:17MAR2016
	IEC 60643-1
	EN 61643-11
	CAN/CSA-C22.2 No. 8:2013 Ed.5

## Mounting

Mounting type	Surface/Panel mounting
---------------	------------------------

# SYS N4 480D - Surge protection device

2800707

<https://www.phoenixcontact.com/us/products/2800707>

## Drawings

Circuit diagram



# SYS N4 480D - Surge protection device



2800707

<https://www.phoenixcontact.com/us/products/2800707>

## Classifications

### ECLASS

ECLASS-13.0	27171202
-------------	----------

### UNSPSC

UNSPSC 21.0	39121620
-------------	----------

# SYS N4 480D - Surge protection device



2800707

<https://www.phoenixcontact.com/us/products/2800707>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	4-Nonylphenol, branched and linear(CAS: n/a)
-------------------------------------	--

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)