

# SYS N4/I 120/208Y - Surge protection device



2800709

<https://www.phoenixcontact.com/us/products/2800709>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Indoor/outdoor lightning current arrester and TVSS system for 120/208-240 V



## Product description

Combination lightning current arrester and TVSS for 120/208-240 V. Components are housed in an IP66/NEMA 4 cabinet and include phase indicator lamps.

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2800709                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | CL01                           |
| Product key                          | CL1621                         |
| GTIN                                 | 4046356642958                  |
| Weight per piece (including packing) | 222.22 g                       |
| Weight per piece (excluding packing) | 222.22 g                       |
| Customs tariff number                | 85363090                       |
| Country of origin                    | DE                             |

# SYS N4/I 120/208Y - Surge protection device



2800709

<https://www.phoenixcontact.com/us/products/2800709>

## Technical data

### Product properties

|                                |  |
|--------------------------------|--|
| Product type                   | Surge protection for NEMA power supply units |
| IEC test classification        | I + II                                       |
| EN type                        | T1   |
| Type                           | Housing for surface mounting                 |
| Surge protection fault message | Remote indication contact                    |

### Electrical properties

|                       |                                     |
|-----------------------|-------------------------------------|
| Nominal voltage $U_N$ | < 240 V                             |
| Fuse                  | 200 kA VSP100, 100 A, 200 kAIC (IR) |

### General

|               |                  |
|---------------|------------------|
| Power Systems | 120/208 V AC Wye |
|---------------|------------------|

### Connection data

|                                       |                      |
|---------------------------------------|----------------------|
| Conductor cross-section flexible min. | 16 mm <sup>2</sup>   |
| Conductor cross-section flexible max. | 35 mm <sup>2</sup>   |
| Conductor cross-section, rigid min.   | 10 mm <sup>2</sup>   |
| Conductor cross-section, rigid max.   | 50 mm <sup>2</sup>   |
| Connection method                     | Screw connection     |
| Conductor cross-section flexible min. | 0.14 mm <sup>2</sup> |
| Conductor cross-section flexible max. | 1.5 mm <sup>2</sup>  |
| Conductor cross-section, rigid min.   | 0.14 mm <sup>2</sup> |
| Conductor cross-section, rigid max.   | 1.5 mm <sup>2</sup>  |

### Dimensions

|        |        |
|--------|--------|
| Width  | 400 mm |
| Height | 500 mm |
| Depth  | 210 mm |

### Material specifications

|                  |       |
|------------------|-------|
| Housing material | Steel |
|------------------|-------|

### Protective circuit

|  |                    |
|--|--------------------|
| Nominal voltage $U_N$                      | 120/208 V AC (Wye) |
| Maximum continuous operating voltage $U_C$ | 275 V AC           |
| Follow current interrupt rating $I_{fi}$   | 50 kA              |
| Response time $t_A$                        | ≤ 25 ns            |

### Environmental and real-life conditions

#### Ambient conditions

|                      |             |
|----------------------|-------------|
| Degree of protection | IP66/NEMA 4 |
|----------------------|-------------|

# SYS N4/I 120/208Y - Surge protection device



2800709

<https://www.phoenixcontact.com/us/products/2800709>

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

## Approvals

### UL specifications

|                                     |                    |
|-------------------------------------|--------------------|
| Short-circuit current rating (SCCR) | 50 kA              |
| UL type                             | type 2             |
| Nominal discharge current $I_n$     | 20 kA              |
| Maximum Surge Current per Phase     | 50 kA              |
| Nominal voltage                     | 120/208 V AC (Wye) |
| Power distribution system           | Wye                |

## Standards and regulations

### Standards

|                       |                                    |
|-----------------------|------------------------------------|
| Standards/regulations | ANSI/UL 1449:2014 Ed.4+R:17MAR2016 |
|                       | IEC 60643-1                        |
|                       | EN 61643-11                        |
|                       | CAN/CSA-C22.2 No. 8:2013 Ed.5      |

## Mounting

|               |                        |
|---------------|------------------------|
| Mounting type | Surface/Panel mounting |
|---------------|------------------------|

# SYS N4/I 120/208Y - Surge protection device

2800709

<https://www.phoenixcontact.com/us/products/2800709>

## Drawings

Circuit diagram



# SYS N4/I 120/208Y - Surge protection device



2800709

<https://www.phoenixcontact.com/us/products/2800709>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171202 |
|-------------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121620 |
|-------------|----------|

# SYS N4/I 120/208Y - Surge protection device



2800709

<https://www.phoenixcontact.com/us/products/2800709>

## Environmental product compliance

### EU RoHS

|   |   |
|---|---|
| Fulfills EU RoHS substance requirements | Not applicable, Not qualified for the European market |
|---|---|

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |  |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a)  |
|                                     | 4-Nonylphenol, branched and linear(CAS: n/a) |
|                                     | Lead(CAS: 7439-92-1)                         |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)