

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Indoor/outdoor lightning current arrester and TVSS system for 240 V Delta system in a NEMA 4X polycarbonate enclosure

## Product description

Combination lightning current arrester and TVSS for 240 Delta.

## Your advantages

- With floating remote indication contact
- Optical, mechanical status indication for the individual arresters

## Commercial data

Item number	2801550
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL01
Product key	CL1212
GTIN	4055626029887
Weight per piece (including packing)	222.222 kg
Weight per piece (excluding packing)	222.222 kg
Customs tariff number	85361010
Country of origin	US

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

## Set consists of

FLT-SEC-T1+T2-3C-350/25-FM - Type 1+2 special combined lightning current and surge arrester

2905469

<https://www.phoenixcontact.com/us/products/2905469>



Plug-in lightning and surge arrester combination, in accordance with Type 1+2/Class I+II, for 3-phase power supply networks, with combined PE and N installed in one conductor (L1, L2, L3, PEN).

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

## Technical data

### Product properties

IEC test classification	I + II
	T1 + T2
	T1
	I
EN type	T1 + T2
	T1
Surge protection fault message	Optical, remote indicator contact
Number of ports	One

### Insulation characteristics

Overvoltage category	III
Pollution degree	2

### Electrical properties

Nominal frequency $f_N$	50 Hz (60 Hz)
Nominal voltage $U_N$	$\leq 240$ V
	240 V

### Indicator/remote signaling

Connection name	Remote fault indicator contact
Switching function	Changeover contact
Maximum operating voltage $U_{max. AC}$	250 V AC
Operating voltage	12 V AC ... 250 V AC
	125 V DC (200 mA DC)
Operating current	10 mA AC ... 1 A AC
	1 A DC (30 V DC)

### Connection data

Connection method	Screw terminal blocks
Screw thread	M5
Tightening torque	4.5 Nm
	40 lb <sub>F</sub> -in. (UL)
Stripping length	18 mm
Conductor cross-section flexible	2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Conductor cross-section rigid	2.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Conductor cross-section AWG	13 ... 2
	12 ... 2 (UL)

### Remote fault indicator contact

Connection method	Plug-in/screw connection via COMBICON
Screw thread	M2
Tightening torque	0.25 Nm

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

Stripping length	7 mm
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16

## Dimensions

Width	360 mm
Height	400 mm
Depth	185 mm

## Material specifications

Flammability rating according to UL 94	V0
CTI value of material	600
Insulating material	PA6.6-FR 20% GF PBT-FR
Material group	I
Housing material	PC PA 6.6-FR 20 % GF PBT-FR

## Protective circuit

Direction of action	3L-N/PE
Nominal voltage $U_N$	240/415 V AC (TN-C)
Nominal frequency $f_N$	50 Hz (60 Hz)
Maximum continuous operating voltage $U_C$ (L-PEN)	350 V AC
Rated load current $I_L$	125 A (< 55 °C)
Nominal discharge current $I_n$ (8/20) $\mu$ s (L-PEN)	25 kA
Follow current quenching capacity $I_{fi}$ (L-PEN)	25 kA (264 V AC) 3 kA (350 V AC)
Short-circuit current rating $I_{SCCR}$	25 kA (264 V AC) 3 kA (350 V AC)
Voltage protection level $U_p$ (L-PEN)	$\leq 1.5$ kV
Residual voltage $U_{res}$	$\leq 1.5$ kV (at $I_n$ ) $\leq 1.2$ kV (at 10 kA) $\leq 1$ kV (at 5 kA) $\leq 0.9$ kV (at 3 kA)
TOV behavior at $U_T$	415 V AC (5 s / withstand mode) 457 V AC (120 min / safe failure mode)
Response time $t_A$ (L-PEN)	$\leq 25$ ns
Max. backup fuse with V-type through wiring	125 A AC (gG) 125 A AC (gG)
Max. backup fuse with branch wiring	315 A AC (gG)

## Additional technical data

Maximum discharge current $I_{max}$ (8/20) $\mu$ s	100 kA
--	--------

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66 (when door is latched and all additional fittings and accessories have similar or better rating.) IP66/NEMA 4X
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %

## Approvals

### UL specifications

Maximum continuous operating voltage MCOV (L-L)	528 V AC
Maximum continuous operating voltage MCOV (L-G)	264 V AC
Short-circuit current rating (SCCR)	50 kA
Voltage protection rating VPR (L-L)	2 kV
Voltage protection rating VPR (L-N)	1.2 kV
Voltage protection rating VPR (L-G)	1200 V
UL type	type 2
Nominal discharge current $I_n$ (L-L)	20 kA
Mode of protection	L-L L-G
Nominal voltage	240 V AC 240/415 V AC
Rated load current $I_L$	50 A
Power distribution system	Delta Wye
Nominal frequency	50/60 Hz
SPD Type	2CA

### UL indicator/remote signaling

Operating voltage	125 V AC
AC operating current	1 A AC

### UL connection data

Tightening torque	40 lb <sub>F</sub> -in.
Conductor cross-section AWG	3 ... 2

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN VDE 0110-1 / IEC 60664-1 / IEC 61643-1
Standards/specifications	IEC 61643-11
Note	2011

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

Standards/specifications	EN 61643-11
Note	2012

## Mounting

Mounting type	Surface/Panel mounting
---------------	------------------------

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

## Classifications

### ECLASS

ECLASS-13.0	27171202
ECLASS-15.0	27171202

### UNSPSC

UNSPSC 21.0	39121620
-------------	----------

# SYS-N4XP FLT-CP 240D - Surge protection device



2801550

<https://www.phoenixcontact.com/us/products/2801550>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)