

IFS-OP-UNIT - Operator interface



2811899

<https://www.phoenixcontact.com/us/products/2811899>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The operator interface facilitates straightforward parameterization and operation of the MACX MCR(-EX)-...-UI(REL)(-UP) on-site, even without software. Can be snapped onto the 35 mm module. Replacement part: 2905872 IFS-BT-PROG-ADAPTER.

Your advantages

- Local display of actual values
- Easy guided operation
- Operating and display unit can be snapped directly onto compatible devices with a housing width of 35 mm
- Installation in zone 2 permitted

Commercial data

Item number	2811899
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C402
Product key	DK111Z
GTIN	4046356308106
Weight per piece (including packing)	64.3 g
Weight per piece (excluding packing)	47.7 g
Customs tariff number	85312095
Country of origin	DE

Technical data

Product properties

Product type	Operator interface
--------------	--------------------

Connection data

PC side

Connection method	S-PORT (socket)
-------------------	-----------------

Measuring transducer side

Connection method	S-PORT (male connector)
-------------------	-------------------------

Dimensions

Width	35 mm
Height	99 mm
Depth	20 mm

Material specifications

Color	gray (RAL 7042)
Housing material	PA 6.6

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C (-4 °F ... 149 °F)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (-40 °F ... 185 °F)
Altitude	≤ 2000 m
Permissible humidity (operation)	90 % (at 25 °C, non-condensing)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	⊕ II 3G Ex nA ic IIC T4 Gc X
Certificate	IBExU 10 ATEX B008 X

IECEX

Identification	Ex nA ic IIC T4 Gc
Certificate	IECEX IBE 10.0012 X

UL, USA/Canada

Identification	UL 508 Listed
	Class I, Div. 2, Groups A, B, C, D T6
	Class I, Zone 2, Group IIC T6

IFS-OP-UNIT - Operator interface



2811899

<https://www.phoenixcontact.com/us/products/2811899>

Shipbuilding approval

Identification	C, EMC2
Certificate	DNV GL 11 564-14HH

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Noise immunity	EN 61000-6-2

Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com