

# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Screw on module for conduit systems, with two conductor protection for a 2-core floating signal circuit. Design: 24 V DC

## Commercial data

Item number	2818122
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CL02
Product key	CL2231
GTIN	4017918148355
Weight per piece (including packing)	295.2 g
Weight per piece (excluding packing)	295.2 g
Customs tariff number	85363010
Country of origin	DE

# S-PT1-2PE-24DC - Surge protection device

2818122

<https://www.phoenixcontact.com/us/products/2818122>

## Technical data

### Notes

#### Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

### Product properties

Product type	Surge protection for MCR technology
Product family	SURGETRAB
IEC test classification	C1
	C2
	C3
	D1
Type	Screw-in module
Number of positions	3
Surge protection fault message	none


### Electrical properties

Nominal voltage $U_N$	24 V DC
-----------------------	---------

### Connection data

Connection method	Screw connection
Conductor cross-section flexible min.	0.14 mm <sup>2</sup>
Conductor cross-section flexible max.	1.5 mm <sup>2</sup>
Conductor cross-section, rigid min.	0.14 mm <sup>2</sup>
Conductor cross-section, rigid max.	1.5 mm <sup>2</sup>

### Dimensions

Dimensional drawing	
Width	33 mm
Height	33 mm
Depth	120 mm

### Mechanical properties

#### Mechanical data

Open side panel	No
-----------------	----

### Protective circuit

Direction of action	Line-Line & Line-Earth Ground
---------------------	-------------------------------

# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

Nominal voltage $U_N$	24 V DC
Maximum continuous operating voltage $U_C$	28 V DC
	20 V AC
Maximum continuous voltage $U_C$ (line-line)	28 V DC
	20 V AC
Nominal current $I_N$	250 mA (25 °C)
Operating effective current $I_C$ at $U_C$	$\leq 5 \mu\text{A}$
Protective conductor current $I_{PE}$	$\leq 2 \mu\text{A}$
Nominal discharge current $I_n$ (8/20) $\mu\text{s}$ (line-line)	10 kA
Nominal discharge current $I_n$ (8/20) $\mu\text{s}$ (line-ground)	10 kA
Total surge current (8/20) $\mu\text{s}$	20 kA
Max. discharge current $I_{max}$ (8/20) $\mu\text{s}$ maximum (line-line)	10 kA
Max. discharge current $I_{max}$ (8/20) $\mu\text{s}$ maximum (line-earth)	10 kA
Nominal pulse current $I_{an}$ (10/1000) $\mu\text{s}$ (line-line)	180 A
Nominal pulse current $I_{an}$ (10/1000) $\mu\text{s}$ (line-earth)	180 A
Output voltage limitation at 1 kV/ $\mu\text{s}$ (line-line) spike	$\leq 60 \text{ V}$
Output voltage limitation at 1 kV/ $\mu\text{s}$ (line-earth) spike	$\leq 450 \text{ V}$
Output voltage limitation at 1 kV/ $\mu\text{s}$ (line-line) static	$\leq 60 \text{ V}$
Residual voltage at $I_n$ (conductor-conductor)	$\leq 40 \text{ V}$
Residual voltage at $I_n$ (conductor-ground)	$\leq 60 \text{ V}$
Residual voltage with $I_{an}$ (10/1000) $\mu\text{s}$ (line-line)	$\leq 25 \text{ V}$
Residual voltage with $I_{an}$ (10/1000) $\mu\text{s}$ (line-earth)	$\leq 20 \text{ V}$
Voltage protection level $U_p$ (line-line)	$\leq 55 \text{ V}$
Voltage protection level $U_p$ (line-earth)	$\leq 550 \text{ V}$
Response time $t_A$ (line-line)	$\leq 1 \text{ ns}$
Response time $t_A$ (line-earth)	$\leq 100 \text{ ns}$
Input attenuation aE, sym.	$\leq 1.6 \text{ dB}$ (up to 500 kHz, 50 $\Omega$ system)
	$\leq 0.6 \text{ dB}$ (up to 200 kHz, 150 $\Omega$ system)
	$\leq 0.2 \text{ dB}$ (up to 50 kHz, 600 $\Omega$ system)
Cut-off frequency $f_g$ (3 dB), sym. in 50 $\Omega$ system	typ. 3.5 MHz
Cut-off frequency $f_g$ (3 dB), sym. in 150 $\Omega$ system	typ. 1.5 MHz
Cut-off frequency $f_g$ (3 dB), sym. in 600 $\Omega$ system	typ. 400 kHz
Capacity (Core-Core)	typ. 1.5 nF
Resistance per path	10 $\Omega$ 5 %
Surge protection fault message	none
Impulse durability (line-line)	C2 - 10 kV / 5 kA
Impulse durability (line-earth)	C2 - 10 kV / 5 kA
	D1 - 2.5 kA
Alternating current carrying capacity (line-earth)	5 A - 1 s

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP40
----------------------	------

# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

## Approvals

### Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D
------------------	------------------------------------

## Standards and regulations

### Standards Information technology specification

Standards/regulations	IEC 61643-21
	IEC 61643-21

### Air clearances and creepage distances

Standards/regulations	VDE 0110-1 / IEC 60664-1
-----------------------	--------------------------

## Mounting

Mounting type	Connection-specific intermediate plugging
---------------	---


# S-PT1-2PE-24DC - Surge protection device

2818122


<https://www.phoenixcontact.com/us/products/2818122>

## Drawings

Dimensional drawing



Circuit diagram



# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2818122>



**UL Listed**

Approval ID: FILE E 138168



**cUL Listed**

Approval ID: FILE E 333250



**UL Listed**

Approval ID: FILE E 333250

# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

## Classifications

### ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

### ETIM

ETIM 10.0	EC001466
-----------	----------

# S-PT1-2PE-24DC - Surge protection device



2818122

<https://www.phoenixcontact.com/us/products/2818122>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)