

PR2-RSC3-LV-230AC/2X21 - Relay module



2834672

<https://www.phoenixcontact.com/us/products/2834672>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 24 V DC version

Pre-assembled relay modules with screw connection, consisting of: relay base, industrial relay with integrated LED and engage/disengage manual activate layer, varistor protective module, and retaining bracket. Input voltage: 230 V AC, 2 changeover contacts, 10 A

Your advantages

- Relay with detectable manual operation and status LED
- With DC types, freewheeling diode is integrated in relay
- 4-changeover contact types with multi-layer gold contacts
- Logical contact arrangement thanks to 1/3-level relay base
- Mechanical switch position indicator

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2834672 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C463 |
| Product key | DK631A |
| GTIN | 4017918996253 |
| Weight per piece (including packing) | 121.85 g |
| Weight per piece (excluding packing) | 118.3 g |
| Customs tariff number | 85364900 |
| Country of origin | CN |

PR2-RSC3-LV-230AC/2X21 - Relay module



2834672


<https://www.phoenixcontact.com/us/products/2834672>

Set consists of

PR2-BSC3/4X21 - Relay base

2833576

<https://www.phoenixcontact.com/us/products/2833576>



Relay base PR2-B, for industrial relay REL-IR with 2 or 4 changeover contacts, 1/3-level design, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

REL-IR/L-230AC/2X21 - Single relay

2834070

<https://www.phoenixcontact.com/us/products/2834070>



Plug-in industrial relays with power contacts, 2 changeover contacts, test button, status LED, mechanical switching position indicator, input voltage: 230 V AC

PR2-RSC3-LV-230AC/2X21 - Relay module

2834672

<https://www.phoenixcontact.com/us/products/2834672>



V-120-230UC - Plug-in module

2833880

<https://www.phoenixcontact.com/us/products/2833880>



Plug-in module, with varistor, input voltage: 120 ... 230 V AC/DC $\pm 20\%$

EL2-P35 - Retaining bracket

2833592

<https://www.phoenixcontact.com/us/products/2833592>



Relay retaining bracket, with eject function and integrated equipment marking area (8 x 25 mm), to suit relay base PR2, for 35 mm high industrial relay

PR2-RSC3-LV-230AC/2X21 - Relay module

2834672

<https://www.phoenixcontact.com/us/products/2834672>



MP 2 - Marker labels

2833644

<https://www.phoenixcontact.com/us/products/2833644>

Equipment marker, labeling surface 9 x 25 mm



Technical data

Product properties

| | |
|-------------------------|---------------------------|
| Product type | Relay Module |
| Application | Universal |
| Operating mode | 100% operating factor |
| Mechanical service life | 5x 10 ⁷ cycles |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 3 |

Data management status

| | |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

Electrical properties

| | |
|---|--|
| Service life electrical | see diagram |
| Maximum power dissipation for nominal condition | 1.15 W |
| Test voltage (Winding/contact) | 2 kV AC (50 Hz, 1 min., winding/contact) |
| Test voltage (Contact/contact) | 2 kV AC (50 Hz, 1 min., contact/contact) |

Input data

Coil side

| | |
|---|------------------------------------|
| Nominal input voltage U _N | 230 V AC |
| Input voltage range | 179.4 V AC ... 345 V AC |
| Drive and function | monostable |
| Typical input current at U _N | 5 mA (at 50 Hz) 4 mA (At 60 Hz) |
| Typical response time | 4 ms ... 10 ms |
| Typical release time range | 3 ms ... 12 ms |
| Protective circuit | Varistor |
| Operating voltage display | LED red |

Output data

Switching

| | |
|-----------------------------|-----------------------|
| Contact switching type | 2 changeover contacts |
| Type of switch contact | Single contact |
| Contact material | Ag |
| Maximum switching voltage | 250 V AC/DC |
| Minimum switching voltage | 5 V |
| Limiting continuous current | 10 A |
| Maximum inrush current | 20 A (15 ms) |
| Min. switching current | 1 mA |

PR2-RSC3-LV-230AC/2X21 - Relay module



2834672

<https://www.phoenixcontact.com/us/products/2834672>

| | |
|---------------------------------------|------------------------|
| Interrupting rating (ohmic load) max. | 240 W (at 24 V DC) |
| | 160 W (at 48 V DC) |
| | 110 W (at 60 V DC) |
| | 72 W (at 110 V DC) |
| | 130 W (at 220 V DC) |
| | 2500 VA (for 250 V AC) |

Connection data

Coil side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 26 ... 14 |

Contact side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 26 ... 14 |

Dimensions

| | |
|--------|---------|
| Width | 27 mm |
| Height | 78.5 mm |
| Depth | 86 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection (Relay) | RT I (Relay) |
| Ambient temperature (operation) | -25 °C ... 60 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|-----------|
| Standards/regulations | IEC 60664 |
| | EN 50178 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

PR2-RSC3-LV-230AC/2X21 - Relay module




2834672

<https://www.phoenixcontact.com/us/products/2834672>

| | |
|-------------------|---------------------------|
| Assembly note | in rows with zero spacing |
| Mounting position | any |


Drawings

Diagram




Operating voltage range of relay $T_u=T_{coil}$

Diagram




- ① Ohmic load
- ② $\cos \phi = 0.4$

AC interrupting rating



- ① Ohmic load
- ② ohmic load, contacts in series
- ③ $L/R < 7$ ms

DC interrupting rating



- ① 250 V AC, ohmic load
- ② 30 V DC, ohmic load

Electrical service life



PR2-RSC3-LV-230AC/2X21 - Relay module

2834672

<https://www.phoenixcontact.com/us/products/2834672>



Circuit diagram



) The contacts 21, 22, 24 are connected to the relay base connections 41, 42, 44.

PR2-RSC3-LV-230AC/2X21 - Relay module



2834672

<https://www.phoenixcontact.com/us/products/2834672>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122334 |
|-------------|----------|

PR2-RSC3-LV-230AC/2X21 - Relay module



2834672

<https://www.phoenixcontact.com/us/products/2834672>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com