

ST-REL3-SG-B 60/21/P - Relay connectors



2824064

<https://www.phoenixcontact.com/us/products/2824064>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay plug, fitted with remanence miniature switching relay, contacts (AgSnO): small to large loads, 1 changeover contact, input voltage 60 V DC, with polarity protection and freewheeling diode, positive switching

The figure shows version ST-REL3-SG-B 24/21/M

Commercial data

Item number	2824064
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6122
GTIN	4017918139346
Weight per piece (including packing)	34.245 g
Weight per piece (excluding packing)	34.245 g
Customs tariff number	85364190
Country of origin	DE

ST-REL3-SG-B 60/21/P - Relay connectors



2824064

<https://www.phoenixcontact.com/us/products/2824064>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Operating mode	100% operating factor
Mechanical service life	approx. 10^7 cycles

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation
------------	------------------

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.54 W
Test voltage (Winding/contact)	2 kV _{rms} (50 Hz, 1 min., winding/contact)
Rated insulation voltage	250 V AC
Rated surge voltage	2.5 kV

Input data

Coil side

Nominal input voltage U_N	60 V DC
Input voltage range	48 V DC ... 66 V DC
Input voltage range in reference to U_N	0.8 ... 1.1
Drive and function	bistable
Typical input current at U_N	typ. 9 mA
Typical response time	5 ms
Typical release time	5 ms
Pulse time range	30 ms ... 5 s
Coil voltage	24 V DC
Protective circuit	Freewheeling diode; Freewheeling diode Reverse polarity protection; Polarity protection diode

Output data

Switching

ST-REL3-SG-B 60/21/P - Relay connectors



2824064

<https://www.phoenixcontact.com/us/products/2824064>

Contact switching type	Single contact, 1 changeover contact
Type of switch contact	Single contact
Contact material	AgSnO
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	5 V (At 5 V) 24 V (at 24 V)
Limiting continuous current	6 A
Maximum inrush current	8 A
Min. switching current	1 mA (at 24 V) 100 mA (At 5 V)
Interrupting rating (ohmic load) max.	144 W (at 24 V DC) 43 W (at 48 V DC) 42 W (at 60 V DC) 55 W (at 110 V DC) 100 W (at 220 V DC) 1500 VA (for 250 V AC)

Switching: when the gold layer is destroyed

Maximum switching voltage	250 V AC/DC
Limiting continuous current	6 A
Maximum inrush current	8 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC) 40 W (at 48 V DC) 35 W (at 60 V DC) 30 W (at 110 V DC) 55 W (at 220 V DC) 1500 VA (for 250 V AC)

Dimensions

Width	20.8 mm
Height	33 mm
Depth	66.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664 IEC 60664A
-----------------------	-------------------------

ST-REL3-SG-B 60/21/P - Relay connectors



2824064

<https://www.phoenixcontact.com/us/products/2824064>

	DIN VDE 0110
	DIN VDE 0109-11, draft
	DIN EN 50178/VDE 0160 (in relevant parts)

Air clearances and creepage distances between the power circuits

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	Plug-in mounting
Assembly note	in rows with zero spacing
Mounting position	any

ST-REL3-SG-B 60/21/P - Relay connectors




2824064

<https://www.phoenixcontact.com/us/products/2824064>

Drawings

Circuit diagram



ST-REL3-SG-B 60/21/P - Relay connectors



2824064

<https://www.phoenixcontact.com/us/products/2824064>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com