

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection plug for base element, for protecting a double conductor of analog telecommunication interfaces.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2838733 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL03 |
| Product key | CL3121 |
| GTIN | 4046356044677 |
| Weight per piece (including packing) | 28.8 g |
| Weight per piece (excluding packing) | 28.94 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

PT 2-TELE-ST - Surge protection plug

2838733

<https://www.phoenixcontact.com/us/products/2838733>

Technical data

Product properties

| | |
|--------------------------------|---|
| Product type | Surge protection for information technology |
| Product family | PLUGTRAB PT |
| IEC test classification | B2 |
| | C1 |
| | C2 |
| | C3 |
| | D1 |
| Type | Male |
| Number of positions | 2 |
| Surge protection fault message | none |
| Wire pairs per module | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |


Electrical properties

| | |
|-----------------------|----------|
| Nominal voltage U_N | 185 V DC |
| | 130 V AC |

Connection data

| | |
|-------------------|-----------|
| Connection method | pluggable |
|-------------------|-----------|

Dimensions

| | |
|------------------------|--|
| Dimensional drawing |  |
| Width | 17.7 mm |
| Height | 45 mm |
| Depth | 52 mm |
| Horizontal pitch | 1 Div. |
| Complete module width | 17.7 mm |
| Complete module height | 90 mm |
| Complete module depth | 65.5 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| | copper color |
| Flammability rating according to UL 94 | V-0 |

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

| | |
|------------------|--------|
| Housing material | PA 6.6 |
|------------------|--------|

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Protective circuit

| | |
|--|--|
| Direction of action | Line-Line & Line-Earth Ground |
| Nominal voltage U_N | 185 V DC |
| | 130 V AC |
| Maximum continuous operating voltage U_C | 185 V DC |
| | 130 V AC |
| Rated current | 450 mA AC (45 °C) |
| | 130 mA DC (45 °C) |
| Operating effective current I_C at U_C | $\leq 10 \mu\text{A}$ |
| Protective conductor current I_{PE} | $\leq 10 \mu\text{A}$ |
| Nominal discharge current I_n (8/20) μs (line-line) | 10 kA |
| Nominal discharge current I_n (8/20) μs (line-ground) | 10 kA |
| Pulse discharge current I_{imp} (10/350) μs (line-line) | 1 kA |
| Pulse discharge current I_{imp} (10/350) μs (line-earth) | 1 kA |
| Total discharge current I_{Total} (8/20) μs | 18 kA |
| Max. discharge current I_{max} (8/20) μs maximum (line-earth) | 18 kA |
| Nominal pulse current I_{an} (10/700) μs (line-line) | 100 A |
| Nominal pulse current I_{an} (10/700) μs (line-earth) | 100 A |
| Output voltage limitation at 1 kV/ μs (line-line) spike | $\leq 300 \text{ V}$ |
| Output voltage limitation at 1 kV/ μs (line-earth) spike | $\leq 300 \text{ V}$ |
| Output voltage limitation at 1 kV/ μs (line-line) static | $\leq 300 \text{ V}$ |
| Output voltage limitation at 1 kV/ μs (line-earth) static | $\leq 300 \text{ V}$ |
| Residual voltage at I_n (conductor-conductor) | $\leq 160 \text{ V}$ (C2 - 10 kV / 5 kA) |
| Residual voltage at I_n (conductor-ground) | $\leq 200 \text{ V}$ (C2 - 10 kV / 5 kA) |
| Voltage protection level U_p (line-line) | $\leq 250 \text{ V}$ (B2 - 1 kV / 25 A) |
| | $\leq 300 \text{ V}$ (B2 - 4 kV / 100 A) |
| | $\leq 270 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 300 \text{ V}$ (C2 - 2 kV/1 kA) |
| | $\leq 320 \text{ V}$ (C2 - 4 kV / 2 kA) |
| | $\leq 330 \text{ V}$ (C2 - 10 kV / 5 kA) |
| Voltage protection level U_p (line-earth) | $\leq 250 \text{ V}$ (B2 - 1 kV / 25 A) |
| | $\leq 300 \text{ V}$ (B2 - 4 kV / 100 A) |
| | $\leq 270 \text{ V}$ (C1 - 1 kV / 500 A) |
| | $\leq 300 \text{ V}$ (C2 - 2 kV/1 kA) |
| | $\leq 320 \text{ V}$ (C2 - 4 kV / 2 kA) |
| | $\leq 330 \text{ V}$ (C2 - 10 kV / 5 kA) |
| Response time t_A (line-line) | $\leq 500 \text{ ns}$ |
| Response time t_A (line-earth) | $\leq 500 \text{ ns}$ |

PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

| | |
|--|---|
| Input attenuation aE, sym. | typ. 0.4 dB (≤ 5 MHz / 100 Ω) |
| Cut-off frequency f _g (3 dB), sym. in 100 Ω system | typ. 20 MHz |
| Capacity (Core-Core) | typ. 30 pF (f=1 MHz / V _R = 0 V) |
| Capacity (Core-Earth) | typ. 30 pF (f=1 MHz / V _R = 0 V) |
| Surge protection fault message | none |
| Impulse durability (line-line) | B2 - 4 kV / 100 A |
| | C1 - 1 kV / 500 A |
| | C2 - 10 kV / 5 kA |
| | C3 - 25 A |
| | D1 - 1 kA |
| Impulse durability (line-earth) | B2 - 4 kV / 100 A |
| | C1 - 1 kV / 500 A |
| | C2 - 10 kV / 5 kA |
| | C3 - 25 A |
| | D1 - 1 kA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Standards and regulations

| | |
|--------------------------|--------------|
| Standards/specifications | IEC 61643-21 |
| Note | 2000 |
| Standards/specifications | EN 61643-21 |
| Note | 2002 |

Mounting

| | |
|---------------|-----------------|
| Mounting type | on base element |
|---------------|-----------------|

PT 2-TELE-ST - Surge protection plug

2838733

<https://www.phoenixcontact.com/us/products/2838733>


Drawings

Dimensional drawing



The figure shows the complete module consisting of a base element and connector

Circuit diagram



PT 2-TELE-ST - Surge protection plug



2838733

<https://www.phoenixcontact.com/us/products/2838733>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27171503 |
| ECLASS-15.0 | 27171503 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

2838733

<https://www.phoenixcontact.com/us/products/2838733>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | a019aefc-4f31-4732-92b0-bf6a402b9381 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.893 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com