


# IB IL DI16-PLSET/ICP - Connector set



2860989

<https://www.phoenixcontact.com/us/products/2860989>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector set, for IB IL DI 16, copper, colored identification.

## Commercial data

Item number	2860989
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR01
Product key	DRI1Z1
GTIN	4017918878887
Weight per piece (including packing)	92.7 g
Weight per piece (excluding packing)	90.9 g
Customs tariff number	85366990
Country of origin	DE

# IB IL DI16-PLSET/ICP - Connector set



2860989

<https://www.phoenixcontact.com/us/products/2860989>

## Technical data

### Product properties

Product type	Connector set
--------------	---------------

### Connection data

Conductor cross-section, rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	28 ... 16
Stripping length	8 mm

# IB IL DI16-PLSET/ICP - Connector set



2860989

<https://www.phoenixcontact.com/us/products/2860989>

## Classifications

### UNSPSC

UNSPSC 21.0	32151602
-------------	----------

# IB IL DI16-PLSET/ICP - Connector set



2860989

<https://www.phoenixcontact.com/us/products/2860989>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)