

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i repeater power supply and input signal conditioner, HART-transparent. Transmits supplied or active 0/4 ... 20 mA signals from the Ex area to a load (active or passive) in the safe area. SIL 2 (1oo1) / SIL 3 (1oo2), wide-range supply.

Your advantages

- 250 Ω resistor that can be activated via DIP switches to increase HART impedance for low-resistance systems
- Up to SIL 2 in accordance with EN 61508
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Wide-range power supply of 19.2 ... 253 V AC/DC
- 3-way electrical isolation
- Plug-in screw or spring-cage connection technology (Push-in technology), with integrated sockets for HART communicators
- 0/4 ... 20 mA input, [Ex ia] IIC (powered or not powered)
- Bidirectional transmission of digital HART communication signals
- 0/4 ... 20 mA output (active or passive), 0/1 ... 5 V, can be selected via DIP switches

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2865793 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C430 |
| Product key | DK1211 |
| GTIN | 4046356324694 |
| Weight per piece (including packing) | 194.2 g |
| Weight per piece (excluding packing) | 194.2 g |
| Customs tariff number | 85437090 |
| Country of origin | DE |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

Technical data

Product properties

| | |
|-----------------|-----------------------|
| Product type | Repeater power supply |
| Product family | MACX Analog |
| Application | Analog IN |
| No. of channels | 1 |
| Configuration | DIP switches |

Electrical properties

| | |
|---|---|
| Electrical isolation | 3-way isolation |
| Electrical isolation between input and output | yes |
| Step response (10-90%) | < 600 μ s (for 4 mA ... 20 mA step) |
| Maximum temperature coefficient | < 0.01 %/K |
| Maximum transmission error | < 0.1 % (of final value) |
| Transmission error, typical | < 0.05 % (of final value) |

Electrical isolation

| | |
|----------------------|-------------------------|
| Test voltage | 2.5 kV AC (50 Hz, 60 s) |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical isolation Input/output/power supply IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Insulation | Safe isolation |

Electrical isolation Input/output IEC/EN 60079-11

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 265 V _{rms} |

Electrical isolation Input/power supply IEC/EN 60079-11

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 265 V _{rms} |

Electrical isolation Output/supply IEC/EN 60079-7

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 60079-7 |
| Rated insulation voltage | 265 V _{rms} |

Supply

| | |
|------------------------------|---|
| Designation | Repeater power supply operation |
| Nominal supply voltage range | 24 V AC/DC ... 230 V AC/DC -20 % ... +10 % (50/60 Hz) |
| Supply voltage range | 19.2 V AC/DC ... 253 V AC/DC (50/60 Hz) |
| Max. current consumption | < 80 mA (24 V DC / 20 mA) |
| Power dissipation | < 1.6 W (24 V DC / 20 mA) |
| Power consumption | < 2.2 W |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

Supply

| | |
|------------------------------|---|
| Designation | Signal conditioner operation |
| Nominal supply voltage range | 24 V AC/DC ... 230 V AC/DC -20 % ... +10 % (50/60 Hz) |
| Supply voltage range | 19.2 V AC/DC ... 253 V AC/DC (50/60 Hz) |
| Max. current consumption | < 45 mA (24 V DC / 20 mA) |
| Power dissipation | < 1.1 W (24 V DC / 20 mA) |

Input data

Signal: Repeater power supply operation

| | |
|----------------------------|--|
| Description of the input | Active current input, intrinsically safe |
| Number of inputs | 1 |
| Current input signal | 4 mA ... 20 mA |
| Transmitter supply voltage | > 16 V (20 mA) > 15.3 V (22.5 mA) |

Signal: Signal conditioner operation

| | |
|--------------------------|--|
| Description of the input | Passive current input, intrinsically safe |
| Current input signal | 0 mA ... 20 mA 4 mA ... 20 mA |
| Voltage drop | < 3.5 V (in input isolating amplifier operation) |

Output data

Signal: Repeater power supply operation

| | |
|--|---|
| Output description | Current output (active and passive) |
| Number of outputs | 1 |
| Voltage output signal | 1 V ... 5 V (internal resistance, 250 Ω , 0.1%) Configurable via DIP switches |
| Current output signal | 4 mA ... 20 mA (active) 4 mA ... 20 mA (14 ... 26 V ext. source voltage) |
| Load/output load current output | < 600 Ω (20 mA) < 525 Ω (22.5 mA) |
| Output ripple | < 20 mV _{rms} |
| Output behavior in the event of an error | 0 mA (Cable break in the input) \geq 22.5 mA (Cable short-circuit in the input) |

Signal: Signal conditioner operation

| | |
|---------------------------------|--|
| Output description | Current output (active and passive) |
| Voltage output signal | 0 V ... 5 V (internal resistance, 250 Ω , 0.1%) 1 V ... 5 V (internal resistance, 250 Ω , 0.1%) |
| Current output signal | 0 mA ... 20 mA (active) 4 mA ... 20 mA (active) 0 mA ... 20 mA (14 ... 26 V ext. source voltage) 4 mA ... 20 mA (14 ... 26 V ext. source voltage) |
| Load/output load current output | < 600 Ω (20 mA) |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

| | |
|--|---|
| | < 525 Ω (22.5 mA) |
| Output ripple | < 20 mV _{rms} |
| Output behavior in the event of an error | 0 mA (Cable break in the input) |
| | 0 mA (Cable short-circuit in the input) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Test socket

| | |
|---------------|------|
| Max. diameter | 2 mm |
|---------------|------|

Ex data

| | |
|-----------------------|----------|
| Ex installation (EPL) | Gc |
| | Div. 2 |
| Ex i circuits (EPL) | [Ga] |
| | [Da] |
| | [Ma] |
| | [Div. 1] |

Safety data: Repeater power supply operation

| | |
|--|--|
| Max. output voltage U_o | 25.2 V |
| Max. output current I_o | 93 mA |
| Max. output power P_o | 587 mW |
| Safety-related maximum voltage U_m | 253 V AC/DC (Supply terminals) |
| | 253 V AC (Output terminals) |
| | 125 V DC (Output terminals) |
| I (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 40 mH / 4.8 μ F |
| IIA (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 26 mH / 2.9 μ F |
| IIB (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 14 mH / 820 nF |
| IIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 3 mH / 107 nF |
| IIA (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 26 mH / 470 nF, 20 mH / 570 nF, 1 mH / 630 nF, 0.5 mH / 720 nF, 0.1 mH / 1.1 μ F, 0.005 mH / 2.9 μ F |
| IIB/III (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 16 mH / 370 nF, 500 μ H / 510 nF, 200 μ H / 660 nF, 100 μ H / 820 nF |
| IIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 2.2 mH / 47 nF, 2 mH / 49 nF, 1 mH / 63 nF, 500 μ H / 80 nF, 200 μ H / 107 nF |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

| | |
|--|--|
| I (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 37 mH / 0.54 μ F, 0.35 mH / 1 μ F, 0.009 mH / 2.9 μ F, 0.001 mH / 4.15 μ F |
| Safety data: Signal conditioner operation | |
| Input voltage U_i | ≤ 30 V |
| Input current I_i | ≤ 150 mA |
| Max. internal inductance L_i | negligible |
| Max. internal capacitance C_i | negligible |
| Safety-related maximum voltage U_m | 253 V AC/DC (Supply terminals) |
| | 253 V AC (Output terminals) |
| | 125 V DC (Output terminals) |

Interfaces

Data communication (bypass)

| | |
|---------------------|-------------------|
| HART function | HART transparency |
| Protocols supported | HART |

Signaling

| | |
|----------------|----------------------------|
| Status display | Green LED (supply voltage) |
|----------------|----------------------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing | |
| Width | 17.5 mm |
| Height | 112.5 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
| Housing material | PA 6.6-FR |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP20 (not assessed by UL) |
| Ambient temperature (operation) | -40 °C ... 60 °C (Any mounting position) |
| | -40 °C ... 70 °C (Derating) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

| | |
|----------------------------------|---|
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |
| Altitude range (≤ 2000 m) | |
| Altitude | ≤ 2000 m (The technical data refers to altitudes ≤ 2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 60 °C -40 °C ... 70 °C (Derating) |
| Rated insulation voltage | 375 V _{PP} (Power supply, input / output) |
| Altitude range (≤ 3000 m) | |
| Height range | > 2000 m ... 3000 m |
| Ambient temperature (operation) | -40 °C ... 54 °C -40 °C ... 63 °C (Derating) |
| Rated insulation voltage | 190 V AC (Power supply, input / output) 110 V DC (Power supply, input / output) |
| Altitude range (≤ 4000 m) | |
| Height range | > 3000 m ... 4000 m |
| Ambient temperature (operation) | -40 °C ... 48 °C -40 °C ... 56 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |
| Altitude range (≤ 5000 m) | |
| Height range | > 4000 m ... 5000 m |
| Ambient temperature (operation) | -40 °C ... 42 °C -40 °C ... 49 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
| Note | and EN 61326 |

ATEX

| | |
|----------------|---|
| Identification | <ul style="list-style-type: none"> Ⓜ II (1) G [Ex ia Ga] IIC Ⓜ II (1) D [Ex ia Da] IIIC Ⓜ II 3(1) G Ex ec [ia Ga] IIC T4 Gc Ⓜ I (M1) [Ex ia Ma] I |
| Certificate | BVS 08 ATEX E 094 X |

IECEX

| | |
|----------------|--|
| Identification | <ul style="list-style-type: none"> [Ex ia Ga] IIC [Ex ia Da] IIIC Ex ec [ia Ga] IIC T4 Gc [Ex ia Ma] I |
| Certificate | IECEX BVS 08.0035X |

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

CCC / China-Ex

| | |
|----------------|-------------------------|
| Identification | [Ex ia Ga] IIC |
| | [Ex ia Da] IIIC |
| | Ex ec [ia Ga] IIC T4 Gc |
| Certificate | 2022122316115974 |

UL, USA/Canada

| | |
|----------------|--|
| Identification | Class I Div 2; IS for Class I, II, III Div 1 |
| Certificate | UL® C.D.-No 83104549 |

Safety Integrity Level (SIL / SILCL, IEC 61508)

| | |
|----------------|------------|
| Identification | 2 |
| Certificate | ZP/C031/20 |

Systematic Capability (SC / SILCL)

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

INMETRO

| | |
|----------------|-------------------------|
| Identification | [Ex ia Ga] IIC |
| | [Ex ia Da] IIIC |
| | Ex ec [ia Ga] IIC T4 Gc |
| Certificate | DNV 18.0138 X |

EMC data

| | |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise immunity | EN 61000-6-2 |
| Note | When being exposed to interference, there may be minimal deviations. |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

Electromagnetic HF field

| | |
|--|--------------------------|
| Designation | Electromagnetic RF field |
| Standards/regulations | EN 61000-4-3 |
| Typical deviation from the measuring range final value | 1 % |

Fast transients (burst)

| | |
|--|-------------------------|
| Designation | Fast transients (burst) |
| Standards/regulations | EN 61000-4-4 |
| Typical deviation from the measuring range final value | 1 % |

Conducted interference

| | |
|--|-------------------------|
| Designation | Conducted interferences |
| Standards/regulations | EN 61000-4-6 |
| Typical deviation from the measuring range final value | 1 % |

Standards and regulations

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

| | |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

GB Standard

| | |
|-----------------------|--------------|
| Standards/regulations | GB/T 3836.1 |
| | GB/T 3836.3 |
| | GB/T 3836.4 |
| | GB/T 16935.1 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply




2865793


<https://www.phoenixcontact.com/us/products/2865793>

Drawings

Dimensional drawing



Diagram




Signal transmission analog and digital at the same time

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply

2865793

<https://www.phoenixcontact.com/us/products/2865793>

Block diagram



MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2865793>

 **UL Listed**
Approval ID: E330267

 **cUL Listed**
Approval ID: E330267


Functional Safety
Approval ID: ZP/C031/20

 **EAC Ex**
Approval ID: RU C-DE.AB72.B.00093


 **IECEx**
Approval ID: IECEx BVS 08.0035X

 **cUL Listed**
Approval ID: E199827

 **UL Listed**
Approval ID: E199827

 **ATEX**
Approval ID: BVS 08 ATEX E094 X

INMETRO
Approval ID: DNV 18.0138 X

 **CCC**
Approval ID: 2022122316115974

INMETRO
Approval ID: DNV 18.0138 X

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210120 |
| ECLASS-15.0 | 27210120 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

MACX MCR-EX-SL-RPSSI-I-UP - Repeater power supply



2865793

<https://www.phoenixcontact.com/us/products/2865793>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 72d31893-5c56-464b-890e-f9f92c20470a |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com