

RAD-ISM-2400-ANT-OMNI-6-0 - Antenna



2885919

<https://www.phoenixcontact.com/us/products/2885919>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Omnidirectional antenna for wall or mast mounting, 2.4 GHz, gain: 6 dBi, degree of protection: IP67, saltwater-resistant, shock- and vibration-resistant, connection: N (female), incl. mounting bracket and mast clamps, ATEX and IECEx approval



Your advantages

- Ideally suited for stationary 2.4 GHz applications
- For use in potentially explosive areas
- Salt water resistant

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2885919 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN23 |
| Product key | DNN2Z1 |
| GTIN | 4046356146319 |
| Weight per piece (including packing) | 394.7 g |
| Weight per piece (excluding packing) | 388.7 g |
| Customs tariff number | 85177100 |
| Country of origin | PL |

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Utilization restriction

| | |
|------------|---|
| CCCex note | Use in potentially explosive areas is not permitted in China. |
|------------|---|

Product properties

| | |
|---------------------------|---|
| Product type | Antenna |
| Scope of supply | included mounting bracket and mast clamps |
| Radiation characteristics | Omnidirectional |
| Gain | 6 dBi |
| Vertical beamwidth | 30 ° |
| Horizontal beamwidth | 360 ° |
| Polarization | Linear vertical |

Electrical properties

| | |
|---|---------------------|
| Frequency band | 2.4 GHz |
| Frequency range | 2.4 GHz ... 2.5 GHz |
| Impedance | 50 Ω |
| Maximum capacity | 25.00 W |
| Voltage standing wave ratio VSWR in a 50 Ω system | ≤ 1.80 |

Connection data

Connection technology

| | |
|-------------------|-------------------------|
| Connection method | N (female) |
| Outside diameter | 25 mm ... 100 mm (Mast) |

Ex data

Safety data

| | |
|--------------------------------|------------|
| Input voltage U_i | 30 V |
| Input current I_i | 600 mA |
| Max. internal inductance L_i | negligible |
| Capacitance C_i | negligible |

Dimensions

| | |
|----------|--------|
| Height | 250 mm |
| Diameter | 22 mm |

External dimensions

| | |
|------------------|-------------------------|
| Outside diameter | 25 mm ... 100 mm (Mast) |
|------------------|-------------------------|

2885919

<https://www.phoenixcontact.com/us/products/2885919>

Material specifications

| | |
|--|-------------------------------|
| Material | Fiberglass-reinforced plastic |
| | V2A |
| | V2A |
| Flammability rating according to UL 94 | HB |

Cable/line

| | |
|------------------|----------------------|
| Connecting cable | no |
| Other resistance | salt water resistant |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 75 °C |
| Wind velocity | 220 km/h |

Approvals

Electronic devices in rail vehicles

| | |
|-----------------------|---------------------------|
| Shock (operation) | IEC 60721-3-4, 4M5 |
| Vibration (operation) | IEC 60721-3-4, 4M5 Random |

Standards and regulations


| | |
|--------------------------|----------------------|
| Other resistance | salt water resistant |
| Standards/specifications | EN 60079-0 |
| | EN 60079-11 |
| Note | Explosion protection |

Mounting

| | |
|---------------|----------------------|
| Mounting type | Panel mounting |
| | Mast mounting |
| Assembly note | Outdoors and indoors |

Drawings

Schematic diagram




Panel mounting

2885919

<https://www.phoenixcontact.com/us/products/2885919>

Schematic diagram



Panel mounting


RAD-ISM-2400-ANT-OMNI-6-0 - Antenna



2885919

<https://www.phoenixcontact.com/us/products/2885919>

Schematic diagram



Mast mounting


RAD-ISM-2400-ANT-OMNI-6-0 - Antenna

2885919

<https://www.phoenixcontact.com/us/products/2885919>



Schematic diagram




Installation example

2885919


<https://www.phoenixcontact.com/us/products/2885919>

Diagram



Horizontal

Diagram



Vertical

RAD-ISM-2400-ANT-OMNI-6-0 - Antenna



2885919

<https://www.phoenixcontact.com/us/products/2885919>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2885919>



IECEx

Approval ID: IECEx IBE 14.0039X



ATEX

Approval ID: IBExU14ATEX1116 X

RAD-ISM-2400-ANT-OMNI-6-0 - Antenna



2885919

<https://www.phoenixcontact.com/us/products/2885919>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19070105 |
| ECLASS-15.0 | 19070105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001698 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223100 |
|-------------|----------|

RAD-ISM-2400-ANT-OMNI-6-0 - Antenna



2885919

<https://www.phoenixcontact.com/us/products/2885919>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 8.855 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com