

# FUSSRIEGEL 14,4 L30 SPERR OG - Base latch



2896998

<https://www.phoenixcontact.com/us/products/2896998>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing for use in distribution boards in accordance with DIN 43880, Base latch, width: 14.4 mm, height: 29.8 mm, depth: 5.9 mm, color: orange (similar RAL 2003)

## Commercial data

Item number	2896998
Packing unit	20 pc
Minimum order quantity	10 pc
Sales key	AC10
Product key	ACHBAZ
GTIN	4046356805551
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.25 g
Customs tariff number	85389099
Country of origin	US

# FUSSRIEGEL 14,4 L30 SPERR OG - Base latch



2896998

<https://www.phoenixcontact.com/us/products/2896998>

## Technical data

### Product properties

Product type	Base latches
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing type	Modular building installation housings
Housing series	BC
Product family	BC

### Dimensions

Width	14.4 mm
Height	29.8 mm
Depth	5.9 mm

### Material specifications

Color (Housing)	orange (RAL 2003)
Material Housing	POM

### Mounting

Mounting type	Snap in
---------------	---------

# FUSSRIEGEL 14,4 L30 SPERR OG - Base latch



2896998

<https://www.phoenixcontact.com/us/products/2896998>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# FUSSRIEGEL 14,4 L30 SPERR OG - Base latch



2896998

<https://www.phoenixcontact.com/us/products/2896998>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)