

# PLC-BPT-230UC/21HC - Relay base



2900259

<https://www.phoenixcontact.com/us/products/2900259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



14 mm PLC basic terminal block for high continuous currents with Push-in connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 1 changeover contact, input voltage 230 V AC/DC

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2900259       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C461          |
| Product key                          | DK62B1        |
| GTIN                                 | 4046356507691 |
| Weight per piece (including packing) | 60.003 g      |
| Weight per piece (excluding packing) | 44.1 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# PLC-BPT-230UC/21HC - Relay base



2900259

<https://www.phoenixcontact.com/us/products/2900259>

## Technical data

### Notes

#### Utilization restriction

|          |   |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

### Product properties

|                |                          |
|----------------|--------------------------|
| Product type   | Relay socket             |
| Product family | PLC-INTERFACE            |
| Application    | High continuous currents |
| Operating mode | 100% operating factor    |

### Electrical properties

|                    |                  |
|--------------------|------------------|
| Protective circuit | Bridge rectifier |
|--------------------|------------------|

### Input data

|                             |   |
|-----------------------------|---|
| Nominal input voltage $U_N$ | 230 V AC/DC<br>The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit |
| Protective circuit          | Bridge rectifier  |
| Nominal input voltage $U_N$ | 230 V AC/DC<br>The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection  |
| Stripping length                 | 10 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup><br>0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule)<br>2x 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup> (TWIN ferrule) |
| Conductor cross-section AWG      | 26 ... 14   |

### Signaling

|                |     |
|----------------|-----|
| Status display | LED |
|----------------|-----|

### Dimensions

|        |       |
|--------|-------|
| Width  | 14 mm |
| Height | 80 mm |
| Depth  | 94 mm |

### Material specifications

# PLC-BPT-230UC/21HC - Relay base



2900259

<https://www.phoenixcontact.com/us/products/2900259>

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -40 °C ... 55 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UKCA

|             |                |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

### Shipbuilding approval

|             |            |
|-------------|------------|
| Certificate | TAE0000196 |
|-------------|------------|

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

### Shipbuilding data

|             |   |
|-------------|---|
| Temperature | D   |
| Humidity    | A   |
| Vibration   | B/C   |
| EMC         | B   |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive         |
| Low Voltage Directive         | Conformance with Low Voltage Directive |

## Standards and regulations

|                       |                |
|-----------------------|----------------|
| Standards/regulations | IEC/EN 60664-1 |
|-----------------------|----------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

# PLC-BPT-230UC/21HC - Relay base



2900259

<https://www.phoenixcontact.com/us/products/2900259>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371603 |
| ECLASS-15.0 | 27371603 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001456 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# PLC-BPT-230UC/21HC - Relay base



2900259

<https://www.phoenixcontact.com/us/products/2900259>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
|                                     | Lead(CAS: 7439-92-1)                        |
| SCIP                                | 7eb2007a-1dfd-4e61-8cd5-7453a3d03349        |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)