

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE for railway applications, consisting of basic terminal block with push-in connection and integrated miniature solid-state relay, range: $0.7 \times U_N$ to $1.25 \times U_N$, temperature range: -25°C to $+70^\circ\text{C}$, 1 N/O contact, input: 110 V DC, output: 3 - 33 V DC/3 A

Your advantages

- Shock resistance in accordance with DIN 50155 (requirements in accordance with EN 61373)
- Temperature range: -25°C ... $+70^\circ\text{C}$
- Input voltage range of $0.7 - 1.25 \times U_N$

Commercial data

Item number	2900380
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C461
Product key	DK62AL
GTIN	4046356508940
Weight per piece (including packing)	28.94 g
Weight per piece (excluding packing)	28.94 g
Customs tariff number	85364900
Country of origin	DE

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Technical data

Product properties

Product type	Solid-state relay module
Product family	PLC-INTERFACE
Application	Railway applications
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.33 W
-------------------------------------------------	--------

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V
Rated surge voltage	4 kV

Input data

Nominal input voltage U_N	110 V DC
Input voltage range in reference to U_N	0.7 ... 1.25 ($t < 1 \text{ s} = 0.6 \dots 1.4 \times U_N$)
Input voltage range	77 V DC ... 137.5 V DC
Switching threshold "0" signal in reference to U_N	≤ 0.3
Switching threshold "1" signal in reference to U_N	≥ 0.6
Typical input current at U_N	3 mA
Typical response time	80 μs
Typical turn-off time	600 μs
Operating voltage display	Yellow LED
Protective circuit	Reverse polarity protection; Polarity protection diode
Transmission frequency	100 Hz

Output data

Contact switching type	1 N/O contact
Design of digital output	electronic
Output nominal voltage	24 V DC
Output voltage range	3 V DC ... 33 V DC ($t < 1 \text{ s} = 1.40 \times U_N$)
Limiting continuous current	3 A (see derating curve)
Surge voltage protection	> 33 V DC
Voltage drop at max. limiting continuous current	< 200 mV
Output circuit	2-conductor, floating

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Protective circuit	Reverse polarity protection; Polarity protection diode
	Surge protection; Suppressor diode

Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
	0.2 mm ² ... 2.5 mm ² (Single ferrule)
	2x 0.5 mm ² ... 1 mm ² (TWIN ferrule)
Conductor cross-section AWG	26 ... 14

Dimensions

Item dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V0 (Housing)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	IEC 60947-5-1
-----------------------	---------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module

2900380

<https://www.phoenixcontact.com/us/products/2900380>

Drawings

Diagram



- ① In rows with zero spacing
- ② in rows with > 20 mm spacing

The figure shows the load current as function of the ambient temperature range PLC-OSP-.../24DC/3RW. Duty cycle: 100% operating factor

Circuit diagram



PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900380>



cULus Listed

Approval ID: E140324



cUL Recognized

Approval ID: E238705



UL Recognized

Approval ID: E238705



UL Listed

Approval ID: FILE E 172140



cUL Listed

Approval ID: FILE E 172140



cULus Listed

Approval ID: E140324



cULus Listed

Approval ID: E140324

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Classifications

ECLASS

ECLASS-13.0	27371604
ECLASS-15.0	27371604

ETIM

ETIM 10.0	EC001504
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

PLC-OPT-110DC/ 24DC/3RW - Solid-state relay module



2900380

<https://www.phoenixcontact.com/us/products/2900380>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	966f6fed-ee09-413d-8e9a-0059074d5116

EF3.1 Climate Change

CO2e kg	0.928 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com