

UM-IC14/8DO/F/LA/S7 - Passive module




2902896

<https://www.phoenixcontact.com/us/products/2902896>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

8-channel DO passive module with signal indicator light and fuse protection



Commercial data

Item number	2902896
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2CZZ
GTIN	4055626164328
Weight per piece (including packing)	125.2 g
Weight per piece (excluding packing)	125.2 g
Country of origin	US

UM-IC14/8DO/F/LA/S7 - Passive module



2902896

<https://www.phoenixcontact.com/us/products/2902896>

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics

Overvoltage category	III, basic insulation (as per EN 50178)
Pollution degree	2

Electrical properties

Operating voltage (DC)	24 V DC
Operating voltage U_{max} (DC)	≤ 30 V DC
Current (per branch)	≤ 0.8 A ≤ 1 A (pluggable fuse protection)

Supported controller: SIEMENS S7-300 / ET 200 M

Suitable I/O card	6ES7322-1BL00-0AA0
	6ES7322-1BH00-0AA0
	6ES7322-1BH01-0AA0
	6ES7322-1BH10-0AA0

Connection data

Field level

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	14

Dimensions

Item dimensions

Width	90 mm
Height	70 mm
Depth	90 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

UM-IC14/8DO/F/LA/S7 - Passive module



2902896

<https://www.phoenixcontact.com/us/products/2902896>

Standards/regulations	IEC 60664
-----------------------	-----------

Mounting

Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM-IC14/8DO/F/LA/S7 - Passive module




2902896

<https://www.phoenixcontact.com/us/products/2902896>

Drawings

Circuit diagram



Block diagram

UM-IC14/8DO/F/LA/S7 - Passive module



2902896

<https://www.phoenixcontact.com/us/products/2902896>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

2902896

<https://www.phoenixcontact.com/us/products/2902896>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com