


P-FLK20/UKK3/PLC/L - Adapter

2904533

<https://www.phoenixcontact.com/us/products/2904533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter solution for contacting double-level terminal blocks with screw connection to a 20-pos. flat-ribbon cable connector



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2904533 |
| Packing unit | 10 pc |
| Minimum order quantity | 40 pc |
| Product key | DK2AF1 |
| GTIN | 4046356860154 |
| Weight per piece (including packing) | 38.4 g |
| Weight per piece (excluding packing) | 38.4 g |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Interface module |
|--------------|------------------|

Insulation characteristics: Air clearances and creepage distances

| | |
|----------------------|-----------------------|
| Insulation | Functional insulation |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|---------|
| Nominal voltage U_N | 50 V DC |
| | 25 V AC |
| Max. current carrying capacity per branch | 1 A |

Air clearances and creepage distances

| | |
|--------------------------|-------------------------|
| Rated insulation voltage | 50 V |
| Rated surge voltage | 0.5 kV (1.2/50 μ s) |

Connection data

Controller level

| | |
|-----------------------|-------------------|
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 20 |
| Pitch | 2.54 mm |

Field level

| | |
|-------------------|-----------|
| Connection method | pluggable |
|-------------------|-----------|

Dimensions

Item dimensions

| | |
|--------|-------|
| Width | 53 mm |
| Height | 65 mm |
| Depth | 33 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------------------------|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | \geq IP54 (Installation location) |
| Ambient temperature (operation) | -20 °C ... 55 °C |
| Altitude | < 2000 m |

Standards and regulations

P-FLK20/UKK3/PLC/L - Adapter



2904533

<https://www.phoenixcontact.com/us/products/2904533>

Air clearances and creepage distances

| | |
|-----------------------|-----------------------|
| Standards/regulations | DIN EN 50178: 1998-04 |
|-----------------------|-----------------------|

Mounting

| | |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

P-FLK20/UKK3/PLC/L - Adapter



2904533

<https://www.phoenixcontact.com/us/products/2904533>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002780 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

P-FLK20/UKK3/PLC/L - Adapter



2904533

<https://www.phoenixcontact.com/us/products/2904533>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com