

# FL-PP-RJ45/RJ45-B - Patch panel

2904933

<https://www.phoenixcontact.com/us/products/2904933>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch panel, narrow overall width, extended temperature range, two RJ45 jacks, 1:1 assignment, all-around shield, CAT5, 10/100 Mbps, DIN rail adapter, IP20

## Product description

Ethernet patch panels enable quick and easy connection between the field cabling and control cabinet cabling. The passive termination panels are a convenient alternative to the on-site assembly of RJ45 connectors.

## Your advantages

- CAT5e
- Mounting on a DIN rail
- 10/100 Mbps
- Easy and convenient extension for RJ45 cable
- 1:1 connection
- Extended temperature range of -40 °C ... 85 °C
- PoE-capable in accordance with IEEE 802.3bt, type 4
- Slim design



## Commercial data

Item number	2904933
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	DN07
Product key	DNC331

# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

GTIN	4046356900836
Weight per piece (including packing)	40.8 g
Weight per piece (excluding packing)	40 g
Customs tariff number	85366990
Country of origin	US

# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

## Technical data

### Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Patch panel
--------------	-------------

### Interfaces


Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Serial transmission speed	10/100 Mbps
Connection method	RJ45 jack
Note on the connection method	CAT5
No. of channels	1
Pin assignment	1:1
Transmission length	100 m (including patch cables)

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Connection method	RJ45 CAT5
No. of channels	1

### Dimensions

Dimensional drawing	
Width	22.5 mm
Height	78 mm
Depth	44 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material (Housing)	PA 6.6-FR

### Cable/line

Cable impedance	100 Ω
-----------------	-------

### Mechanical properties

# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

## Mechanical data

Insertion/withdrawal cycles	≤ 2500
-----------------------------	--------

## Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 25g, 11 ms period, half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-40 °C ... 85 °C
Permissible humidity (operation)	25 % ... 95 % (non-condensing)

## Approvals

### Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# FL-PP-RJ45/RJ45-B - Patch panel


2904933

<https://www.phoenixcontact.com/us/products/2904933>



## Drawings

Dimensional drawing



Slim design


# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

Block diagram



Circuit diagram

# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

## Classifications

### ECLASS

ECLASS-13.0	19170112
ECLASS-15.0	19170112

### ETIM

ETIM 10.0	EC001128
-----------	----------

### UNSPSC

UNSPSC 21.0	43223300
-------------	----------

# FL-PP-RJ45/RJ45-B - Patch panel



2904933

<https://www.phoenixcontact.com/us/products/2904933>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)