

# UM-D37M/DS/FU/LED/AO/C300/L - Termination board



2905243

<https://www.phoenixcontact.com/us/products/2905243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

16-channel module for Honeywell C300 analog output cards with disconnect, test points, socketed 500 mA fuses and fuse status indicator.



## Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters
- UM-PRO housing
- DIN rail mounting, includes grounding foot
- LED blown fusing indication
- Per channel shield connection
- Per channel disconnects with test points
- Per channel pluggable 500 mA fusing

## Commercial data

Item number	2905243
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218H
GTIN	4046356947091
Weight per piece (including packing)	470.5 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85371098
Country of origin	US

2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	37
No. of channels	16

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	500 mA (fuse limited)
Max. total current of voltage supply	4 A (via D-SUB)

Supported controller: HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TAOX01 (non-redundant)
	TAOX11 (redundant)
	TAOX51 (non-redundant)
	TAOX61 (redundant)
	TAON01 (non-redundant)
	TAON11 (redundant)

Supported controller: HONEYWELL Experion LX Series 8

Suitable I/O card	8X-TAOXA1
	8X-TAOXB1

### Connection data

#### Field level

Connection method	Screw connection with disconnect knife
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

### Signaling

Status display	no
Status display present	yes, if the fuse fails

### Dimensions

2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Item dimensions

Width	104 mm
Height	142.3 mm
Depth	79 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any


# UM-D37M/DS/FU/LED/AO/C300/L - Termination board



2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Drawings




# UM-D37M/DS/FU/LED/AO/C300/L - Termination board



2905243

<https://www.phoenixcontact.com/us/products/2905243>



2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905243>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2905243

<https://www.phoenixcontact.com/us/products/2905243>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ab5fd5b7-eed4-4c31-92f0-c5631af27749

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)