

VIP-CAB-FLK40/EZ-DR/20,0M/S - Cable



2905830

<https://www.phoenixcontact.com/us/products/2905830>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled shielded round cable with additional shield connection and two 40-pos. socket strips (1:1 connection). One socket strip is molded (90° outlet), cable length: 20 m

Your advantages

- 40-pos.
- 1:1 connection

Commercial data

Item number	2905830
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2AH2
GTIN	4046356999007
Weight per piece (including packing)	3,085 g
Weight per piece (excluding packing)	3,085 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Product type	System cable
--------------	--------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (DC)	≤ 24 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 0.5 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

Cable/line

Cable length	20 m
--------------	------

40X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	40
Shielded	yes
Cable type	40X0.14 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	40x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.80 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray

VIP-CAB-FLK40/EZ-DR/20,0M/S - Cable



2905830

<https://www.phoenixcontact.com/us/products/2905830>

Conductor material	Tin-plated Cu litz wires
Cable resistance	$\leq 145 \Omega/\text{km}$ (at 20 °C)
Insulation resistance	$\geq 20 \text{ M}\Omega \cdot \text{km}$ (20 °C)
Smallest bending radius, fixed installation	101 mm
Smallest bending radius, movable installation	182 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of $\geq 18x$ outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Connection data

Flat-ribbon cable connector

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	40
Exit angle	90 °
Insertion/withdrawal cycles	> 200
Pitch	2.54 mm

Flat-ribbon cable connector

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 200
Pitch	2.54 mm

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Diagram



Maximum permissible current per path in uncoiled state

VIP-CAB-FLK40/EZ-DR/20,0M/S - Cable



2905830

<https://www.phoenixcontact.com/us/products/2905830>

Classifications

ECLASS

ECLASS-13.0

27242220

UNSPSC

UNSPSC 21.0

26121600

VIP-CAB-FLK40/EZ-DR/20,0M/S - Cable



2905830

<https://www.phoenixcontact.com/us/products/2905830>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com