

# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE module intended for use with Honeywell Experion C300 16-channel analog input cards. Channels 13.....16 feature differential inputs.



## Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters
- UM-PRO housing
- DIN rail mounting, includes grounding foot
- LED blown fusing indication
- Per channel shield connection
- Per channel disconnects with test points
- Per channel pluggable 500 mA fusing
- Conformal coating of PCB

## Commercial data

Item number	2906183
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BZZ
GTIN	4055626080659
Weight per piece (including packing)	420 g
Weight per piece (excluding packing)	400 g
Customs tariff number	85369010
Country of origin	US

# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

## Technical data

### Product properties

Product type	Interface module
Number of positions	37
No. of channels	16

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	500 mA (fuse limited)

Supported controller: HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TAIX01 (non-redundant)
	TAIX11 (redundant)
	TAIX51 (non-redundant)
	TAIX61 (redundant)
	TAIN01 (non-redundant)
	TAIN11 (redundant)

Supported controller: HONEYWELL Experion LX Series 8

Suitable I/O card	8X-TAIXA1
	8X-TAIXB1

### Connection data

#### Field level

Connection method	Screw connection with disconnect knife
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

### Signaling

Status display	no
Status display present	yes, if the fuse fails

### Dimensions

#### Item dimensions

Width	124 mm
-------	--------

# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

Height	142.3 mm
Depth	79 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

## Notes

General	Standard or halogen-free cables
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

## Drawings




# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

Circuit diagram



# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UM-D37M/DS/FU/LED/AID4/C3/L C - Termination board



2906183

<https://www.phoenixcontact.com/us/products/2906183>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bc9cb6ee-405a-4a16-ad8e-5c13d8cda7e5

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)