

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled shielded round cable; controller: Emerson Delta V S-Series; connection 1: IDC/FLK socket strip (2x 24-position); connection 2: IDC/FLK socket strip (2x 24-position); cable length: 1 m



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2906951 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK221K |
| GTIN | 4055626144849 |
| Weight per piece (including packing) | 202.5 g |
| Weight per piece (excluding packing) | 202.5 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|----------------------------------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A (Uncoiled, see derating) |
| Current (Per path, 70°C) | ≤ 0.6 A (Uncoiled, see derating) |

Supported controller: EMERSON DeltaV

| | |
|-------------------|-------------|
| Suitable I/O card | SE4053S2B11 |
| | SE4083S2B11 |

Cable/line

| | |
|--------------|-----|
| Cable length | 1 m |
|--------------|-----|

50X0.14 [PVC]

| | |
|---------------------------------|--------------------------------|
| UL AWM Style | 2464/1061 |
| Number of positions | 50 |
| Shielded | yes |
| Cable type | 50X0.14 [PVC] |
| Conductor type | Assembled shielded round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 50x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 11.00 mm ±0.3 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

| | |
|---|--|
| Smallest bending radius, fixed installation | 114 mm |
| Smallest bending radius, movable installation | 205 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of $\geq 18x$ outside diameter) |
| Halogen-free | no |
| Flame resistance | IEC 60332-1-2 (raw cable) |
| | VDE 0842, Part 332-1-2 (raw cable) |
| | IEC 60332-3-22 (raw cable) |
| | UL VW-1 |
| | CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Cable for one module |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 2 |
| Number of positions | 24 |
| Conductor cross-section AWG | 26 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | IDC/FLK socket strip |
| Number of connections | 2 |
| Number of positions | 24 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Drawings

Connection diagram

| FLK24 X1 A | FLK24 X3 B | FLK24 X2 C | FLK24 X4 D | Conductor color |
|---------------|---------------|---------------|---------------|-----------------|
| PIN 1 | PIN 1 | | | black |
| PIN 2 | PIN 2 | | | brown |
| PIN 3 | PIN 3 | | | red |
| PIN 4 | PIN 4 | | | orange |
| PIN 5 | PIN 5 | | | yellow |
| PIN 6 | PIN 6 | | | green |
| PIN 7 | PIN 7 | | | blue |
| PIN 8 | PIN 8 | | | violet |
| PIN 9 | PIN 9 | | | gray |
| PIN 10 | PIN 10 | | | white |
| PIN 11 | PIN 11 | | | white-black |
| PIN 12 | PIN 12 | | | white-brown |
| PIN 13 | PIN 13 | | | white-red |
| PIN 14 | PIN 14 | | | white-orange |
| PIN 15 | PIN 15 | | | white-yellow |
| PIN 16 | PIN 16 | | | white-green |
| PIN 17 | PIN 17 | | | white-blue |
| PIN 18 | PIN 18 | | | white-violet |
| PIN 19 | PIN 19 | | | white-gray |
| PIN 20 | PIN 20 | | | brown-black |
| PIN 21 | PIN 21 | | | brown-red |
| PIN 22 | PIN 22 | | | brown-orange |
| PIN 23 | PIN 23 | | | brown-yellow |
| PIN 24 | PIN 24 | | | brown-green |
| | | PIN 1 | PIN 1 | brown-blue |
| | | PIN 2 | PIN 2 | brown-violet |
| | | PIN 3 | PIN 3 | brown-gray |
| | | PIN 4 | PIN 4 | brown-white |
| | | PIN 5 | PIN 5 | green-black |
| | | PIN 6 | PIN 6 | green-brown |
| | | PIN 7 | PIN 7 | green-red |
| | | PIN 8 | PIN 8 | green-orange |
| | | PIN 9 | PIN 9 | green-blue |
| | | PIN 10 | PIN 10 | green-violet |
| | | PIN 11 | PIN 11 | green-gray |
| | | PIN 12 | PIN 12 | green-white |
| | | PIN 13 | PIN 13 | yellow-black |
| | | PIN 14 | PIN 14 | yellow-brown |
| | | PIN 15 | PIN 15 | yellow-red |
| | | PIN 16 | PIN 16 | yellow-orange |
| | | PIN 17 | PIN 17 | yellow-blue |
| | | PIN 18 | PIN 18 | yellow-violet |
| | | PIN 19 | PIN 19 | yellow-gray |
| | | PIN 20 | PIN 20 | yellow-white |
| | | PIN 21 | PIN 21 | gray-black |
| | | PIN 22 | PIN 22 | gray-brown |
| | | PIN 23 | PIN 23 | gray-red |
| | | PIN 24 | PIN 24 | gray-orange |

2906951

<https://www.phoenixcontact.com/us/products/2906951>

Diagram



Maximum permissible current per path in uncoiled state

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906951>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: E238705

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 125 V | 1 A | - | - |



cUL Listed

Approval ID: E238705

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 125 V | 1 A | - | - |

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242220 |
| ECLASS-15.0 | 27242220 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000237 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

CABLE-2FLK24/2FLK24/DV/ 1,0M/S - Cable



2906951

<https://www.phoenixcontact.com/us/products/2906951>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com