

# UM-D25SUB/F/DO - Output module



2908548

<https://www.phoenixcontact.com/us/products/2908548>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital VARIOFACE output module, with COMBICON screw connection and a 25-pos. D-SUB socket strip for ABB S800 I/O modules.

## Commercial data

Item number	2908548
Packing unit	1 pc
Minimum order quantity	10 pc
Product key	DK2AZZ
GTIN	4055626307282
Country of origin	DE

# UM-D25SUB/F/DO - Output module



2908548

<https://www.phoenixcontact.com/us/products/2908548>

## Technical data

### Product properties

Product type	Interface module
--------------	------------------

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V AC/DC
Max. current carrying capacity per branch	1 A
Max. total current of all branches	2.5 A

#### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 $\mu$ s)

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Number of positions	52
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	D-SUB socket strip
Number of connections	1
Number of positions	25

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

Width	139 mm
Height	90 mm
Depth	65 mm

### Material specifications

# UM-D25SUB/F/DO - Output module



2908548

<https://www.phoenixcontact.com/us/products/2908548>

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	max. 2000 m

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# UM-D25SUB/F/DO - Output module



2908548

<https://www.phoenixcontact.com/us/products/2908548>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)