

# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protection in accordance with Class E<sub>A</sub> (CAT6<sub>A</sub>), for Gigabit Ethernet (up to 10 Gbps), token ring, FDDI/CDDI, ISDN, DS1. Suitable for Power over Ethernet (PoE++/4PPoE) "Mode A" and "Mode B". RJ45 intermediate plug with separate grounding cable and ground connection snap-on foot for NS 35 DIN rails.

## Your advantages

- Can be installed in a control cabinet by removing the ground connection adapter
- Suitable for category 6 high-speed data networks

## Commercial data

Item number	2908726
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL24
Product key	CL3112
GTIN	4055626345963
Weight per piece (including packing)	314.857 g
Weight per piece (excluding packing)	314.1 g
Customs tariff number	85363010
Country of origin	DE

# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

## Technical data

### Product properties

Product type	Surge protection for information technology
Product family	DATATRAB
IEC test classification	B2
	C1
	C2
	C3
	D1
Type	Attachment plug for DIN rail mounting
Number of positions	8
Surge protection fault message	none
Wire pairs per module	4


### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Connection data

Connection method	RJ45
-------------------	------

### Dimensions

Dimensional drawing	
Width	25 mm
Height	102 mm
Depth	63.5 mm

### Material specifications

Color	silver-colored
Housing material	Die-cast zinc

### Mechanical properties

#### Mechanical data

Open side panel	No
-----------------	----

### Protective circuit

Direction of action	Line-Line & Line-Ground/Shield
---------------------	--------------------------------

# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

Maximum continuous voltage $U_C$ (line-line)	$\leq 3.3$ V DC ( $\pm 60$ V DC/PoE+)
Rated current	$\leq 1.5$ A (25 °C)
Operating effective current $I_C$ at $U_C$	$\leq 1$ $\mu$ A
Protective conductor current $I_{PE}$	$\leq 400$ $\mu$ A
Nominal discharge current $I_n$ (8/20) $\mu$ s (line-line)	100 A
Nominal discharge current $I_n$ (8/20) $\mu$ s (line-ground)	2 kA (per signal pair)
Pulse discharge current $I_{imp}$ (10/350) $\mu$ s (line-earth)	1 kA
Total discharge current $I_{Total}$ (8/20) $\mu$ s	10 kA
Nominal pulse current $I_{an}$ (10/700) $\mu$ s (line-line)	$\leq 40$ A
Nominal pulse current $I_{an}$ (10/700) $\mu$ s (line-earth)	$\leq 160$ A
Output voltage limitation at 1 kV/ $\mu$ s (line-line) spike	$\leq 85$ V (PoE)
Output voltage limitation at 1 kV/ $\mu$ s (line-earth) spike	$\leq 700$ V
Output voltage limitation at 1 kV/ $\mu$ s (line-line) static	$\leq 9$ V
Output voltage limitation at 1 kV/ $\mu$ s (line-earth) static	$\leq 700$ V
Residual voltage at $I_n$ (conductor-conductor)	$\leq 15$ V
	$\leq 100$ V (PoE)
Voltage protection level $U_p$ (line-line)	$\leq 9$ V (B2 - 1 kV / 25 A)
	$\leq 100$ V (B2 - 1 kV / 25 A - PoE)
	$\leq 12$ V (C3 - 20 A)
Voltage protection level $U_p$ (line-earth)	$\leq 900$ V (B2 - 4 kV / 100 A)
	$\leq 700$ V (C2 - 4 kV / 2 kA)
	$\leq 1$ kV (C3 - 80 A)
Response time $t_A$ (line-line)	$\leq 1$ ns
Response time $t_A$ (line-earth)	$\leq 100$ ns
Input attenuation aE, sym.	$\leq 1$ dB (up to 100 MHz/direct measuring)
	$\leq 1$ dB (up to 250 MHz/direct measuring)
	$\leq 3$ dB (up to 500 MHz/direct measuring)
Near-end crosstalk attenuation	$\geq 35$ dB (250 MHz/100 $\Omega$ /link)
	$\geq 45$ dB (100 MHz / 100 $\Omega$ / Link)
	$\geq 27$ dB (500 MHz / 100 $\Omega$ / Link)
	$\geq 39$ dB (250 MHz/100 $\Omega$ /direct measuring)
Capacity (Core-Core)	typ. 12 pF (f= 1 MHz / VR= 0 V)
Capacity (Core-Earth)	typ. 2 pF (f= 1 MHz / VR= 0 V)
Surge protection fault message	none
Impulse durability (line-line)	B2 - 1 kV / 25 A
	C3 - 20 A
Impulse durability (line-earth)	B2 - 4 kV / 100 A
	C2 - 4 kV / 2 kA
	C3 - 80 A
	D1 - 1 kA

## Environmental and real-life conditions

### Ambient conditions

# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	≤ 4000 m (amsl)
Permissible humidity (operation)	5 % ... 85 %

## Standards and regulations

Standards/specifications	IEC 61643-21
Note	2000 + corrigendum 2001 + A1:2008, modified + A2:2012
Standards/specifications	EN 61643-21
Note	2001 + A1:2009 + A2:2013
Standards/specifications	EN 50173-1
Note	2002
Standards/specifications	ISO/IEC 11801-Am.1
Note	2006

## Mounting

Mounting type	Connection-specific attachment plug and DIN rail, 35 mm
---------------	---

# DT-LAN-CAT.6A - Surge protection device




2908726


<https://www.phoenixcontact.com/us/products/2908726>

## Drawings

Dimensional drawing



Circuit diagram



# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

## Classifications

### ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

### ETIM

ETIM 10.0	EC001625
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# DT-LAN-CAT.6A - Surge protection device



2908726

<https://www.phoenixcontact.com/us/products/2908726>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a)-I, 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)