

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



NAMUR isolation switch amplifier for operating proximity sensors and switches. The signals are transmitted per channel to the control level via 1 transistor output (passive). number of channels: 2, Standard configuration, 3-way isolation, Line fault detection, Safety Integrity Level (SIL, IEC 61508): 2, Systematic Capability: 3, Push-in connection

Your advantages

- Power supply and error indication possible via DIN rail connector
- Up to SIL 2 in accordance with EN 61508
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Line fault detection (LFD), can be activated/deactivated, error indicated by flashing red LED with disabling of transistor output
- Input for NAMUR proximity sensors (EN 60947-5-6), floating contacts or contacts with resistance circuit
- LED indicators for supply voltage, switching state, and malfunction in accordance with NAMUR NE 44
- 2-channel
- Transistor signal output (passive); up to 5 kHz
- 3-way electrical isolation
- Direction of operation can be selected (operating or closed circuit current behavior)

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2924281 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C402 |
| Product key | DK1113 |
| GTIN | 4046356491754 |
| Weight per piece (including packing) | 163.5 g |
| Weight per piece (excluding packing) | 169.1 g |
| Customs tariff number | 85365019 |
| Country of origin | DE |

2924281

<https://www.phoenixcontact.com/us/products/2924281>

Technical data

Product properties

| | |
|-----------------|----------------------------|
| Product type | Isolating switch amplifier |
| Product family | MACX Analog |
| Application | Digital IN |
| No. of channels | 2 |
| Configuration | DIP switches |

System properties

Functionality

| | |
|---------------|--------------|
| Configuration | DIP switches |
|---------------|--------------|

Electrical properties

| | |
|---|----------------------|
| Electrical isolation | 3-way isolation |
| Electrical isolation between input and output | yes |
| Line monitoring | Line fault detection |

Electrical isolation

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical isolation Input/output IEC/EN 60079-7

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-7 |
| Rated insulation voltage | 265 V _{PP} |

Electrical isolation Input/supply, DIN rail connector IEC/EN 60079-7

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-7 |
| Rated insulation voltage | 265 V _{PP} |

Electrical isolation Input/output/supply, DIN rail connector IEC/EN 61010-1

| | |
|--------------------------|-------------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Test voltage | 2.5 kV AC (50 Hz, 60 s) |
| Insulation | Safe isolation |

Electrical isolation Output 1/output 2 IEC/EN 61010-1

| | |
|--------------------------|-----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 50 V _{rms} |
| Test voltage | 1 kV AC (50 Hz, 60 s) |
| Insulation | Basic insulation |

Supply

| | |
|--------------------------|-------------------------|
| Nominal supply voltage | 24 V DC -20 % ... +25 % |
| Supply voltage range | 19.2 V DC ... 30 V DC |
| Max. current consumption | < 34 mA (24 V DC) |

| | |
|-------------------|-----------|
| Power dissipation | ≤ 1000 mW |
| Power consumption | 0.85 W |

Input data

Signal: NAMUR

| | |
|---|---|
| Number of inputs | 2 |
| Available input sources | NAMUR proximity sensors (IEC/EN 60947-5-6) floating switch contacts Switch contacts with resistance circuit |
| Switching threshold "0" signal current | < 1.2 mA (blocking) |
| Switching threshold "1" signal, current | > 2.1 mA (conductive) |
| Short-circuit current | 8 mA |
| Switching hysteresis | < 0.2 mA |
| Line fault detection | < 0.05 mA ... 0.35 mA (Line break) < 100 Ω ... 360 Ω (Short circuit) Activated /deactivated via DIP switch |
| Open-circuit voltage | 8 V DC |

Output data

Switching: Transistor

| | |
|---------------------------|-----------------------------|
| Output description | passive |
| Minimum switching voltage | 3 V DC |
| Maximum switching voltage | 30 V DC |
| Drop (ΔU) | < 1.4 V |
| Max. switching current | 50 mA (short-circuit-proof) |
| Min. switching current | 5 mA (short-circuit-proof) |
| Switching frequency | ≤ 5 kHz |

Signal

| | |
|-------------------|---|
| Number of outputs | 2 |
|-------------------|---|

Connection data

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.25 mm ² ... 0.34 mm ² (TWIN ferrule without plastic sleeve) 0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve) |
| Conductor cross-section AWG | 24 ... 14 24 ... 22 (TWIN ferrule without plastic sleeve) 20 ... 16 (TWIN ferrule with plastic sleeve) |

Ex data

| | |
|-----------------------|----|
| Ex installation (EPL) | Gc |
|-----------------------|----|

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

| | |
|--|--------|
| | Div. 2 |
|--|--------|

Interfaces


Data

| | |
|-----------------|---|
| No. of channels | 0 |
|-----------------|---|

Signaling

| | |
|----------------|------------------------------|
| Status display | Green LED (supply voltage) |
| | LED yellow (switching state) |
| | Red LED (line errors) |

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 12.5 mm |
| Height | 107.9 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
| Housing material | PA 6.6-FR |

Characteristics

Safety data

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
|------------------------------|---|

Safety data

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 2 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP20 (not assessed by UL) |
| Ambient temperature (operation) | -40 °C ... 60 °C (Any mounting position) |
| | -40 °C ... 70 °C (Derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

Altitude range (≤ 2000 m)

| | |
|---------------------------------|---|
| Altitude | ≤ 2000 m (The technical data refers to altitudes ≤ 2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 60 °C -40 °C ... 70 °C (Derating) |
| Rated insulation voltage | 265 V AC/DC ($U_{\text{Isolation "ec"}}$: Supply, input / output) |

Altitude range (≤ 3000 m)

| | |
|---------------------------------|---|
| Height range | > 2000 m ... 3000 m |
| Ambient temperature (operation) | -40 °C ... 54 °C -40 °C ... 63 °C (Derating) |
| Rated insulation voltage | 190 V AC/DC ($U_{\text{Isolation "ec"}}$: Supply, input / output) |

Altitude range (≤ 4000 m)

| | |
|---------------------------------|--|
| Height range | > 3000 m ... 4000 m |
| Ambient temperature (operation) | -40 °C ... 48 °C -40 °C ... 56 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC ($U_{\text{Isolation "ec"}}$: Supply, input / output) |

Altitude range (≤ 5000 m)

| | |
|---------------------------------|--|
| Height range | > 4000 m ... 5000 m |
| Ambient temperature (operation) | -40 °C ... 42 °C -40 °C ... 49 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC ($U_{\text{Isolation "ec"}}$: Supply, input / output) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
| Note | and EN 61326 |

ATEX

| | |
|----------------|--------------------------|
| Identification | ⊕ II 3 G Ex ec IIC T4 Gc |
| Certificate | IBExU 08 ATEX 1100 X |

IECEX

| | |
|----------------|--------------------|
| Identification | Ex ec IIC T4 Gc |
| Certificate | IECEX IBE 08.0005X |

CCC / China-Ex

| | |
|----------------|------------------|
| Identification | Ex ec IIC T4 Gc |
| Certificate | 2022122310115713 |

UL, USA/Canada

| | |
|----------------|---------------------------------------|
| Identification | UL 508 Listed |
| | UL 61010 Listed |
| | Class I, Div. 2, Groups A, B, C, D T4 |

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

| | |
|--|-------------------------------|
| | Class I, Zone 2, Group IIC T4 |
|--|-------------------------------|

Shipbuilding approval

| | |
|-------------|-------------------|
| Certificate | DNV GL TAA00000AG |
|-------------|-------------------|

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|-----------------------|
| Identification | 2 |
| Certificate | IN-AT-AS-MRL-25-00008 |

Systematic Capability

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

INMETRO

| | |
|----------------|-----------------|
| Identification | Ex ec IIC T4 Gc |
| Certificate | DNV 18.0141 X |

Shipbuilding data

| | |
|-------------|---|
| Temperature | B |
| Humidity | B |
| Vibration | A |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

EMC data

| | |
|-------------------------------|--------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise immunity | EN 61000-6-2 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

Electromagnetic HF field

| | |
|-----------------------|--------------------------|
| Designation | Electromagnetic RF field |
| Standards/regulations | EN 61000-4-3 |
| Evaluation criterion | A |

Fast transients (burst)

| | |
|-----------------------|-------------------------|
| Designation | Fast transients (burst) |
| Standards/regulations | EN 61000-4-4 |
| Evaluation criterion | A |

Conducted interference

| | |
|-----------------------|-------------------------|
| Designation | Conducted interferences |
| Standards/regulations | EN 61000-4-6 |
| Evaluation criterion | A |

Standards and regulations

| | |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

GB Standard

| | |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
| | GB/T 3836.3 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

Drawings

Dimensional drawing




MACX MCR-SL-2NAM-T-SP - Isolation switch amplifier



2924281

<https://www.phoenixcontact.com/us/products/2924281>

Block diagram



2924281

<https://www.phoenixcontact.com/us/products/2924281>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2924281>

 **UL Listed**
Approval ID: E330267


 **cUL Listed**
Approval ID: E330267

 **CCC**
Approval ID: 2022122310115713

DNV
Approval ID: TAA00000AG

TUEV Austria FS
Approval ID: IN-AT-AS-MRL-25-0008

 **cUL Listed**
Approval ID: E199827

 **UL Listed**
Approval ID: FILE E 199827

INMETRO
Approval ID: DNV 18.0141 X

 **IECEx**
Approval ID: IECEx IBE 08.0005X

 **ATEX**
Approval ID: IBEExU 08 ATEX 1100

2924281

<https://www.phoenixcontact.com/us/products/2924281>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210121 |
| ECLASS-15.0 | 27210121 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001485 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 85228004-b55b-4a9a-afbe-5bcf39ffabfc |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 4.867 kg CO2e |
|---------|---------------|