

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Primary-switched MINI POWER power supply for DIN rail mounting, input: 1-phase, output: 10 V DC ... 15 V DC/2 A

## Product Description

MINI POWER power supplies for MCR technology


In measurement and control technology (MCR), modular electronics housing has become the industry standard. MINI POWER is the power supply unit to go with it. The devices are flexible, thanks to special voltages and special versions.

## Your advantages

- ✓ Easy-maintenance connection technology thanks to keyed COMBICON connectors
- ✓ Remote monitoring of output voltage via switching output



## Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 1 pc  |
| GTIN         | <br>4 017918 925192 |
| GTIN         | 4017918925192   |

## Technical data

### Dimensions

|                                  |               |
|----------------------------------|---------------|
| Width                            | 45 mm         |
| Height                           | 99 mm         |
| Depth                            | 107 mm        |
| Installation distance right/left | 0 mm / 0 mm   |
| Installation distance top/bottom | 50 mm / 50 mm |

### Ambient conditions

|  |  |
|--|--|
| Degree of protection                           | IP20   |
| Ambient temperature (operation)                | -25 °C ... 70 °C (> 60 °C Derating: 2.5 %/K) |
| Ambient temperature (storage/transport)        | -40 °C ... 85 °C                             |
| Max. permissible relative humidity (operation) | ≤ 95 % (at 25 °C, non-condensing)            |

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

## Technical data

### Input data

|  |   |
|--|---|
| Nominal input voltage range              | 100 V AC ... 240 V AC                     |
| Input voltage range                      | 85 V AC ... 264 V AC                      |
|  | 90 V DC ... 350 V DC                      |
| AC frequency range                       | 45 Hz ... 65 Hz                           |
| Current consumption                      | 0.4 A (120 V AC)                          |
|  | 0.2 A (230 V AC)                          |
|  | 0.4 A (90 V DC)                           |
|  | 0.1 A (350 V DC)                          |
| Nominal power consumption                | 44 VA                                     |
| Inrush current                           | < 15 A (typical)                          |
| Mains buffering time                     | > 20 ms (120 V AC)                        |
|  | > 120 ms (230 V AC)                       |
| Input fuse                               | 2 A (slow-blow, internal)                 |
| Recommended breaker for input protection | 6 A ... 16 A (Characteristics B, C, D, K) |

### Output data

|   |   |
|---|---|
| Nominal output voltage                            | 12 V DC $\pm$ 1 %   |
|   | 10 V DC $\pm$ 1 %   |
|   | 15 V DC $\pm$ 1 %   |
| Setting range of the output voltage ( $U_{Set}$ ) | 10 V DC ... 15 V DC (> 12 V DC, constant capacity restricted)   |
| Nominal output current ( $I_N$ )                  | 2 A (-25 °C ... 60 °C)  |
| POWER BOOST ( $I_{Boost}$ )                       | 2.3 A (-25°C ... 40°C permanent )                               |
| Derating  | 60 °C ... 70 °C (2.5%/K)  |
| Connection in parallel                            | Yes, for assembling redundant systems and increasing efficiency |
| Connection in series                              | yes   |
| Residual ripple                                   | < 20 mV <sub>PP</sub> (20 MHz)                                  |
| Output power                                      | 30 W  |
| Typical response time                             | < 1 s   |
| Peak switching voltages nominal load              | < 100 mV <sub>PP</sub> (20 MHz)                                 |
| Maximum power dissipation in no-load condition    | < 1 W   |
| Power loss nominal load max.                      | < 7 W   |

### General

|                                 |  |
|---------------------------------|--|
| Net weight                      | 0.25 kg                                  |
| Operating voltage display       | Green LED                                |
| Efficiency                      | > 86 % (for 230 V AC and nominal values) |
| MTBF (IEC 61709, SN 29500)      | > 507000 h (40 °C)                       |
| Insulation voltage input/output | 4 kV (type test)                         |
|                                 | 3 kV (routine test)                      |
| Degree of protection            | IP20                                     |
| Protection class                | II (in closed control cabinet)           |

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

## Technical data

### General

|                       |  |
|-----------------------|--|
| Mounting position     | horizontal DIN rail NS 35, EN 60715            |
| Assembly instructions | alignable: horizontally 0 mm, vertically 50 mm |

### Connection data, input

|                                       |                            |
|---------------------------------------|----------------------------|
| Connection method                     | Pluggable screw connection |
| Conductor cross section solid min.    | 0.2 mm <sup>2</sup>        |
| Conductor cross section solid max.    | 2.5 mm <sup>2</sup>        |
| Conductor cross section flexible min. | 0.2 mm <sup>2</sup>        |
| Conductor cross section flexible max. | 2.5 mm <sup>2</sup>        |
| Conductor cross section AWG min.      | 24                         |
| Conductor cross section AWG max.      | 12                         |
| Stripping length                      | 7 mm                       |
| Screw thread                          | M3                         |

### Connection data, output

|                                       |                            |
|---------------------------------------|----------------------------|
| Connection method                     | Pluggable screw connection |
| Conductor cross section solid min.    | 0.2 mm <sup>2</sup>        |
| Conductor cross section solid max.    | 2.5 mm <sup>2</sup>        |
| Conductor cross section flexible min. | 0.2 mm <sup>2</sup>        |
| Conductor cross section flexible max. | 2.5 mm <sup>2</sup>        |
| Conductor cross section AWG min.      | 24                         |
| Conductor cross section AWG max.      | 12                         |
| Stripping length                      | 7 mm                       |
| Screw thread                          | M3                         |

### Connection data for signaling

|                                       |                     |
|---------------------------------------|---------------------|
| Conductor cross section solid min.    | 0.2 mm <sup>2</sup> |
| Conductor cross section solid max.    | 2.5 mm <sup>2</sup> |
| Conductor cross section flexible min. | 0.2 mm <sup>2</sup> |
| Conductor cross section flexible max. | 2.5 mm <sup>2</sup> |
| Conductor cross section AWG min.      | 24                  |
| Conductor cross section AWG max.      | 12                  |
| Screw thread                          | M3                  |

### Standards

|  |                            |
|--|----------------------------|
| EMC requirements for noise immunity  | EN 61000-6-2               |
| Standard - Electrical safety   | EN 60950-1/VDE 0805 (SELV) |
| Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations | EN 50178/VDE 0160 (PELV)   |
| Standard – Safety extra-low voltage  | EN 60950-1 (SELV)          |
|  | EN 60204 (PELV)            |
| Standard - Safe isolation  | DIN VDE 0100-410           |
| Standard – Limitation of mains harmonic currents   | EN 61000-3-2               |

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

## Technical data

### Standards

|                   |            |
|-------------------|------------|
| Rail applications | EN 50121-4 |
|-------------------|------------|

### Conformance/approvals

|              |  |
|--------------|--|
| UL approvals | UL/C-UL listed UL 508  |
|              | UL/C-UL Recognized UL 60950-1  |
|              | UL ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D (Hazardous Location) |

### EMC data


|                               |   |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU         |
| Low Voltage Directive         | Conformance with Low Voltage Directive 2014/35/EC |

### Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | Lead 7439-92-1  |
| China RoHS | Environmentally Friendly Use Period = 25;   |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings

Block diagram



## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27040701 |
| eCl@ss 4.0    | 27143100 |
| eCl@ss 4.1    | 27143100 |
| eCl@ss 5.0    | 27143100 |
| eCl@ss 5.1    | 27143100 |
| eCl@ss 6.0    | 27049000 |
| eCl@ss 7.0    | 27049002 |
| eCl@ss 9.0    | 27040701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001039 |
| ETIM 3.0 | EC001039 |
| ETIM 4.0 | EC000599 |

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 6.0 | EC002540 |
| ETIM 7.0 | EC002540 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211502 |
| UNSPSC 7.0901 | 39121004 |
| UNSPSC 11     | 39121004 |
| UNSPSC 12.01  | 39121004 |
| UNSPSC 13.2   | 39121004 |
| UNSPSC 18.0   | 39121004 |
| UNSPSC 19.0   | 39121004 |
| UNSPSC 20.0   | 39121004 |
| UNSPSC 21.0   | 39121004 |

## Approvals

### Approvals

#### Approvals

UL Listed / UL Recognized / cUL Recognized / cUL Listed / EAC / EAC / cULus Recognized / cULus Listed

#### Ex Approvals

UL Listed / cUL Listed / cULus Listed

### Approval details

|           |  |   |               |
|-----------|--|---|---------------|
| UL Listed |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 123528 |
|-----------|--|---|---------------|

|               |  |   |               |
|---------------|--|---|---------------|
| UL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 214596 |
|---------------|--|---|---------------|

|                |  |   |               |
|----------------|--|---|---------------|
| cUL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 214596 |
|----------------|--|---|---------------|

|            |  |   |               |
|------------|--|---|---------------|
| cUL Listed |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 123528 |
|------------|--|---|---------------|

# Power supply unit - MINI-PS-100-240AC/10-15DC/2 - 2938756

## Approvals

|     |  |               |
|-----|--|---------------|
| EAC |  | EAC-Zulassung |
|-----|--|---------------|

|     |  |                     |
|-----|--|---------------------|
| EAC |  | RU*DE*08.B.01873/19 |
|-----|--|---------------------|

|                  |  |  |
|------------------|--|--|
| cULus Recognized |  |  |
|------------------|--|--|

|              |  |  |
|--------------|--|--|
| cULus Listed |  |  |
|--------------|--|--|

## Accessories

### Accessories

#### Device protection

Type 3 surge protection device - PLT-SEC-T3-230-FM-UT - 2907919



Type 2/3 surge protection, consisting of protective plug and base element with screw connection. For single-phase power supply network with integrated status indicator and remote signaling. Nominal voltage: 230 V AC/DC

Type 3 surge protection device - TTC-6P-T3-24DC-PT-I - 1027586



Type 3 surge protection, consisting of protective plug and base element, with integrated status indicator for 24 V DC power supplies

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>