

# EMG 90-DIO 32M/LP - Diode block

2954785

<https://www.phoenixcontact.com/us/products/2954785>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Lamp test module, 2 diodes with common cathode: with 16 pairs, with common triggering

## Commercial data

Item number	2954785
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK66M1
GTIN	4017918085124
Weight per piece (including packing)	165.2 g
Weight per piece (excluding packing)	165.2 g
Customs tariff number	85411000
Country of origin	DE

# EMG 90-DIO 32M/LP - Diode block



2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Technical data

### Product properties

Product type	Lamp testing module
--------------	---------------------

### Insulation characteristics

Pollution degree	2
------------------	---

### Input data

#### Diode

Diode type	1 N 4007
Max. operating voltage $U_{max}$	250 V AC
Peak reverse voltage per diode	1300 V
Reverse current per diode	$\leq 5 \mu\text{A}$
Conducting state voltage per diode	approx. 0.8 V
Conducting state current per diode	0.7 A (with single load) 0.2 A (with simultaneous loads)

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Dimensions

Width	90 mm
Height	75 mm
Depth	55 mm

### Material specifications

Color	green (RAL 6021)
-------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

### Approvals

#### CE

Certificate	CE-compliant
Note	and EN 61326

# EMG 90-DIO 32M/LP - Diode block



2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# EMG 90-DIO 32M/LP - Diode block




2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Drawings

### Circuit diagram



# EMG 90-DIO 32M/LP - Diode block



2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2954785>



**EAC**

Approval ID: RU\*DE\*08.B.01841/19

# EMG 90-DIO 32M/LP - Diode block



2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Classifications

### ECLASS

ECLASS-13.0	27371010
ECLASS-15.0	27371010

### ETIM

ETIM 10.0	EC002878
-----------	----------

### UNSPSC

UNSPSC 21.0	32151500
-------------	----------

# EMG 90-DIO 32M/LP - Diode block



2954785

<https://www.phoenixcontact.com/us/products/2954785>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	254ff472-f2de-400e-aec5-09ae4d953f77

### EF3.1 Climate Change

CO2e kg	1.993 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)