

PLC-BSC- 12DC/21HC - Relay base

2967769

<https://www.phoenixcontact.com/us/products/2967769>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



14 mm PLC basic terminal block for high continuous currents with screw connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 1 changeover contact, input voltage 12 V DC

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2967769 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C461 |
| Product key | DK6211 |
| GTIN | 4017918174248 |
| Weight per piece (including packing) | 65.54 g |
| Weight per piece (excluding packing) | 57.65 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

PLC-BSC- 12DC/21HC - Relay base



2967769

<https://www.phoenixcontact.com/us/products/2967769>

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|-----------------------|-----------------------------------|
| Product type | Relay socket |
| Product family | PLC-INTERFACE |
| Application | High continuous currents |
| Set comprises | 2967617 PLC-RSC- 12DC/21HC |
| Operating mode | 100% operating factor |
| Compatible components | Miniature relay, REL-MR-12DC/21HC |

Insulation characteristics

| | |
|------------------|---|
| Pollution degree | 3 |
|------------------|---|

Electrical properties

| | |
|--------------------|--|
| Protective circuit | Damping diode, polarity protection diode |
|--------------------|--|

Input data

| | |
|-----------------------------|--------------------|
| Nominal input voltage U_N | 12 V DC |
| Protective circuit | Freewheeling diode |
| Nominal input voltage U_N | 12 V DC |

Output data

| | |
|-----------------------|-----------------------------------|
| Compatible components | Miniature relay, REL-MR-12DC/21HC |
|-----------------------|-----------------------------------|

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| | 0.2 mm ² ... 2.5 mm ² (Single ferrule) |
| | 2x 0.5 mm ² ... 1.5 mm ² (TWIN ferrule) |
| Conductor cross-section AWG | 26 ... 14 |
| Tightening torque | 0.6 Nm ... 0.8 Nm |

Signaling

| | |
|----------------|-----|
| Status display | LED |
|----------------|-----|

Dimensions

PLC-BSC- 12DC/21HC - Relay base



2967769

<https://www.phoenixcontact.com/us/products/2967769>

| | |
|--------|-------|
| Width | 14 mm |
| Height | 80 mm |
| Depth | 94 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -40 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

UKCA

| | |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

Shipbuilding approval

| | |
|-------------|------------|
| Certificate | TAE0000196 |
|-------------|------------|

Corrosive gas test

| | |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
| | EN 60068-2-60 |

Shipbuilding data

| | |
|-------------|---|
| Temperature | D |
| Humidity | A |
| Vibration | B/C |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

EMC data

| | |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive |
| Low Voltage Directive | Conformance with Low Voltage Directive |

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

PLC-BSC- 12DC/21HC - Relay base



2967769

<https://www.phoenixcontact.com/us/products/2967769>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

PLC-BSC- 12DC/21HC - Relay base



2967769

<https://www.phoenixcontact.com/us/products/2967769>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
| | Lead(CAS: 7439-92-1) |
| SCIP | 1dfaae66-7d44-42ca-86e2-3f0b7bcda3bd |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com