

# PLC-BSC- 12DC/21-21 - Relay base



2967251

<https://www.phoenixcontact.com/us/products/2967251>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



14 mm PLC basic terminal block with screw connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 2 changeover contacts, input voltage 12 V DC

## Commercial data

Item number	2967251
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C461
Product key	DK6212
GTIN	4017918163488
Weight per piece (including packing)	63.48 g
Weight per piece (excluding packing)	55.8 g
Customs tariff number	85366990
Country of origin	DE

# PLC-BSC- 12DC/21-21 - Relay base



2967251

<https://www.phoenixcontact.com/us/products/2967251>

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---------------------------------------------------------------------------

### Product properties

Product type	Relay socket
Product family	PLC-INTERFACE
Application	Universal
Set comprises	2967235 PLC-RSC- 12DC/21-21 2967277 PLC-RSC- 12DC/21-21AU
Operating mode	100% operating factor
Compatible components	Miniature relay, REL-MR-12DC/21-21AU, REL-MR-12DC/21-21

#### Insulation characteristics

Pollution degree	3
------------------	---

### Input data

Nominal input voltage $U_N$	12 V DC
Protective circuit	Freewheeling diode
Nominal input voltage $U_N$	12 V DC

### Output data

Compatible components	Miniature relay, REL-MR-12DC/21-21AU, REL-MR-12DC/21-21
-----------------------	---------------------------------------------------------

### Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule) 2x 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule)
Conductor cross-section AWG	26 ... 14
Tightening torque	0.6 Nm ... 0.8 Nm

### Signaling

Status display	LED
----------------	-----

### Dimensions

Width	14 mm
Height	80 mm

# PLC-BSC- 12DC/21-21 - Relay base



2967251

<https://www.phoenixcontact.com/us/products/2967251>

Depth	94 mm
-------	-------

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94 (Housing)	V0 (Housing)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UKCA

Certificate	UKCA-compliant
-------------	----------------

### Shipbuilding approval

Certificate	TAE0000196
-------------	------------

### Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
	EN 60068-2-60

### Shipbuilding data

Temperature	D
Humidity	A
Vibration	B/C
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# PLC-BSC- 12DC/21-21 - Relay base



2967251

<https://www.phoenixcontact.com/us/products/2967251>

## Classifications

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# PLC-BSC- 12DC/21-21 - Relay base



2967251

<https://www.phoenixcontact.com/us/products/2967251>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	9814a9eb-0f36-41e2-96b8-562a5c94c47b

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)